APC Rack PDU, Basic, Zero U, 11 kW, 230V, (36) C13 & (6) C19 power distribution unit (PDU) 42 AC outlet(s) 0U Black



Brand : APC

Product code: AP7557

Product name : Rack PDU, Basic, Zero U, 11 kW, 230V, (36) C13 & (6) C19

Rack PDU, Basic, Zero U, 11 kW, 230V, (36) C13 & (6) C19

APC Rack PDU, Basic, Zero U, 11 kW, 230V, (36) C13 & (6) C19 power distribution unit (PDU) 42 AC outlet(s) 0U Black:

APC Basic Rack PDU , Input: 400V 3PH , Input Connections: IEC 309 16A 3P+N+PE , Cord Length: 3 feet (0.91 meters) , Output: 230V , Output Connections: IEC 320 C13,IEC 320 C19.

- Low Cost Power Distribution.
- Vertical mounting capability.
- Toolless mounting capability.
- Multi-branch power input.

APC Rack PDU, Basic, Zero U, 11 kW, 230V, (36) C13 & (6) C19. PDU types: Basic, Rack capacity: 0U, Mounting: Vertical. AC outlets quantity: 42 AC outlet(s), AC outlet types: C13 coupler, C19 coupler, Input connection type: IEC 309 16A 3P+N+PE. Cable length: 0.91 m. Nominal input voltage: 400 V, AC input frequency: 47/63 Hz, Nominal output voltage: 230 V. Certification: C-tick,CCC,CE,GOST,MIC,Queensland Australia,VD

Design	
PDU types *	Basic
Rack capacity *	0U
Mounting	Vertical
Product colour	Black
Ports & interfaces	
AC outlets quantity *	42 AC outlet(s)
AC outlet types *	C13 coupler, C19 coupler
Input connection type	IEC 309 16A 3P+N+PE
Output connections	(36) IEC 320 C13 (6) IEC 320 C19
Features	
Cable length	0.91 m
Power	
Nominal input voltage *	400 V
AC input frequency	47/63 Hz
Nominal output voltage	230 V
Load capacity	11040 VA
Maximum input current per phase	16 A

Power	
Maximum total current draw per phase	16 A
Maximum power	11000 W
Certificates	
Certification	C-tick,CCC,CE,GOST,MIC,Queensland Australia,VD
Operational conditions	
Operating temperature (T-T)	-5 - 45 °C
Storage temperature (T-T)	-25 - 65 °C
Operating relative humidity (H-H)	5 - 95%
Storage relative humidity (H-H)	5 - 95%
Weight & dimensions	
Width	56 mm
Depth	44 mm
Height	1619 mm
Weight	5.45 kg

0731304254102

731304254102

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date