APC Smart UPS 750VA 230V USB with UL approval

Brand : APC

Product code: SUA750IX38

Product name : Smart UPS 750VA 230V USB with UL approval



Smart UPS 750VA 230V USB with UL approval

APC Smart UPS 750VA 230V USB with UL approval:

Intelligent and efficient power protection enabling multi-regional deployment.
APC Smart UPS 750VA 230V USB with UL approval. Output power capacity: 0.75 kVA, Output power: 500 W, Input frequency: 50/60 Hz. AC outlet types: IEC 60320. Typical backup time at full load: 4.8 min, Typical backup time at half load: 16.4 min, Battery recharge time: 3 h. Product colour: Black. Certification: C-tick,CE,EN 50091-1,EN 50091-2,EN 55022 Class A,GOST,IEC 60950,VDE

Features	
Output power capacity *	0.75 kVA
Output power *	500 W
Input frequency *	50/60 Hz
Surge energy rating	340 J
Audible alarm(s)	✔
Ports & interfaces	
AC outlet types	IEC 60320
Battery	
Typical backup time at full load	4.8 min
Typical backup time at half load	16.4 min
Battery recharge time	3 h
Hot-swap battery	✔
Design	
Product colour *	Black
LED indicators	✔
Operational conditions	
Operating temperature (T-T)	0 - 40 °C
Storage temperature (T-T)	-15 - 45 °C

Operational conditions	
Operating altitude	0 - 3000 m
Non-operating altitude	0 - 15000 m
Certificates	
Certification	C-tick,CE,EN 50091-1,EN 50091-2,EN 55022 Class A,GOST,IEC 60950,VDE
Weight & dimensions	
Weight	13.2 kg
Packaging data	
Package weight	14.6 kg
Logistics data	
Harmonized System (HS) code	85078000
Total carbon footprint (kg of CO2e)	664.38
Other features	
Output connections	6 x IEC 320 C13 1 x IEC Jumpers
Input connection type	IEC-320-C14 inlet
Dimensions (WxDxH)	137 x 358 x 157 mm
Nominal output voltage	230 V
Nominal input voltage	230 V
Package dimensions (WxDxH)	270 x 500 x 290 mm

0731304253365

731304253365

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date