APC Symmetra PX48 Battery Frame with 9 Battery modules & Startup



Brand : APC

Product code: SYCFXR48-9

Product name : APC Symmetra PX48 Battery Frame with 9 Battery modules & Startup

APC Symmetra PX48 Battery Frame with 9 Battery modules & Startup

APC Symmetra PX48 Battery Frame with 9 Battery modules & Startup:

Hot-swappable batteries
Ensures clean, uninterrupted power to protected equipment while batteries are being replaced

Battery modules connected in parallel
Delivers higher availability through redundant batteries.

User-replaceable batteries
Increases availability by allowing a trained user to perform upgrades and replacements of the batteries reducing Mean Time to Repair (MTTR)

Temperature-compensated battery charging
Prolongs battery life by regulating the charge voltage according to battery temperature.

Intelligent battery management
Maximizes battery performance, life, and reliability through intelligent, precision charging.

InfraStruXure Manager Compatible
Enables centralized management via the APC InfraStruXure Manager.

Battery	
Battery technology	Sealed Lead Acid (VRLA)
Battery capacity	31104 Ah
Design	
Form factor *	42U
Product colour *	Black
Operational conditions	
Operating temperature (T-T)	0 - 40 °C
Storage temperature (T-T)	-15 - 45 °C
Operating relative humidity (H-H)	0 - 95%
Storage relative humidity (H-H)	0 - 95%

Operational conditions	
Operating altitude	0 - 999.9 m
Certificates	
Certification	CE,EN/IEC 62040-2,EN/IEC 62040-3,EN/IEC 62040-1-1,UL 1778
Weight & dimensions	
Weight	1252 kg
Packaging data	
Package weight	1351 kg
Other features	
Battery type	VRLA
Dimensions (WxDxH)	600 x 1070 x 1991 mm
Package dimensions (WxDxH)	848 x 1210 x 2134 mm



0731304269038



731304269038



8592978248116

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date