Epson Flippers PicturePack 150 sheets T5846



Brand : Epson **Product family:** Flippers **Product code:** C13T58464010

Product name : PicturePack 150 sheets T5846

PicturePack 150 sheets T5846

Epson Flippers PicturePack 150 sheets T5846:

Epson Original ink cartridges are optimally suited to your printer. These highly reliable cartridges guarantee long printout life and trouble-free printing for many years to come.
Epson Flippers PicturePack 150 sheets T5846. Printing colours: Black, Cyan, Magenta, Yellow, Quantity per pack: 1 pc(s)

Features	
Print technology	Inkjet printing
Compatibility *	PictureMate 240, 260, 280
Quantity per pack *	1 pc(s)
Type *	Original
Ink type	Pigment-based ink
Printing colours *	Black, Cyan, Magenta, Yellow
Brand compatibility *	Epson
OEM code	C13T58464010
Country of origin	China
Colour	✓

Weight & dimensions	
Width	192 mm
Depth	70 mm
Height	142 mm
Weight	750 g

Packaging data	
Package width	150 mm
Package depth	77 mm
Package height	210 mm

Packaging data	
Package weight	0.68 g

Logistics data	
Pallet gross width	80 cm
Pallet gross length	120 cm
Pallet gross height	135 cm
Products per pallet	540 pc(s)
Master (outer) case width	195 mm
Master (outer) case length	370 mm
Master (outer) case height	150 mm
Products per master (outer) case	5 pc(s)
Harmonized System (HS) code	84439990
Pallet width (UK)	100 cm
Pallet length (UK)	120 cm
Pallet height (UK)	135 cm
Products per pallet (UK)	540 pc(s)
Products per pallet layer	60 pc(s)
Products per pallet layer (UK)	60 pc(s)
Minimum order quantity	5 pc(s)

8715946361000

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date