APC NetShelter SX, Server Rack Enclosure, 48U, Black, 2258H x 600W x 1070D mm





Brand : APC

Product code: AR3107

Product name : APC NetShelter SX, Server Rack Enclosure, 48U, Black, 2258H x 600W x 1070D mm

APC NetShelter SX, Server Rack Enclosure, 48U, Black, 2258H x 600W x 1070D mm

APC NetShelter SX, Server Rack Enclosure, 48U, Black, 2258H x 600W x 1070D mm:

An industry standard rack AR3107 with the most features for speed of deployment and installation. Ready for high density environments. 48U height allows for an additional 6U of rack mounting space maximizing u-space per rack footprint.
APC NetShelter SX, Server Rack Enclosure, 48U, Black, 2258H x 600W x 1070D mm. Type: Freestanding rack, Rack capacity: 48U, Maximum weight capacity: 1704 kg. Weight: 138.2 kg. Product colour: Black

Features	
Rack capacity *	48U
Type *	Freestanding rack
Maximum weight capacity *	1704 kg
Product colour	Black
Weight & dimensions	
Size (imperial)	48.3 cm (19")
Width	600 mm
Depth	1070 mm
Height	2258 mm
Weight	138.2 kg
Mounting depth (min)	19.1 cm
Mounting depth (max)	91.5 cm

Packaging data	
Package weight	157.7 kg
Technical details	
Total carbon footprint (kg of CO2e)	478.45
Logistics data	
Harmonized System (HS) code	85381000
Other features	
Dimensions (WxDxH)	600 x 1070 x 2258 mm
Package dimensions (WxDxH)	899 x 1219 x 2385 mm
Dynamic load	1022
Static load	1704



0731304226383



731304226383

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date