Epson Seahorse Singlepack Cyan T0482





Brand : Epson **Product family:** Seahorse **Product code:** C13T04824020

Product name : Singlepack Cyan T0482

Singlepack Cyan T0482

Epson Seahorse Singlepack Cyan T0482:

Epson Original ink cartridges are optimally suited to your printer. These highly reliable cartridges guarantee long printout life and trouble-free printing for many years to come.
Epson Seahorse Singlepack Cyan T0482. Printing colours: Cyan, Quantity per pack: 1 pc(s)

Features	
Print technology	Inkjet printing
Quantity per pack *	1 pc(s)
Colour ink cartridges quantity	1
Type *	Original
Printing colours *	Cyan
Brand compatibility *	Epson
OEM code	C13T04824020
Country of origin	Mexico
Colour	✓
Weight & dimensions	
Width	246 mm
Depth	116 mm
Height	145 mm
Weight	59 g
Packaging data	
Package width	30 mm
Package depth	140 mm
Package height	110 mm
Package type	Blister

Other features	
Certification	CE
Logistics data	
Pallet gross width	80 cm
Pallet gross length	120 cm
Pallet gross height	176 cm
Products per pallet	2400 pc(s)
Master (outer) case width	120 mm
Master (outer) case length	260 mm
Master (outer) case height	146 mm
Products per master (outer) case	100 pc(s)
Harmonized System (HS) code	84439990
Pallet width (UK)	100 cm
Pallet length (UK)	120 cm
Pallet height (UK)	176 cm
Products per pallet (UK)	2400 pc(s)
Products per pallet layer	240 pc(s)
Products per pallet layer (UK)	240 pc(s)
Minimum order quantity	8 pc(s)

8715946358864

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date