APC DLRT5KRMXLI uninterruptible power supply (UPS) Double-conversion (Online) 5 kVA 4500 W

Brand : APC

Product code: DLRT5KRMXLI

Product name : DLRT5KRMXLI



- Boost and trim automatic voltage regulation (AVR)
- Intelligent battery management
- Power conditioning
- Temperature-compensated battery charging
- Automatic restart of loads after UPS shutdown
- Automatic self-test
- Cold-start capable
- Disconnected battery notification

3U, 4500 Watt/5000 VA, AC 230 V, Sinewave, black

APC DLRT5KRMXLI uninterruptible power supply (UPS) Double-conversion (Online) 5 kVA 4500 W:

In addition to legendary reliability and manageability, Smart-UPS have extremely high efficiency at low, medium and high load levels making them ideal for today's multi-core or virtualized servers that have varying load consumption. Rack mounted Smart-UPS are ideal for powering Blade or density optimized servers in a distributed power protection environment as the primary or redundant protection. Smart-UPS models have long been considered the benchmark for all network and server UPS's. Smart-UPS feature a 16-segment LED display, extended range automatic voltage regulation (AVR), and pure sine wave output on battery.

Features	
UPS topology *	Double-conversion (Online)
Output power capacity *	5 kVA
Output power *	4500 W
Waveform *	Sine
Input operation voltage (max) *	230 V
Output operation voltage (max)	230 V
Automatic Voltage Regulation (AVR)	✔
Audible alarm(s)	✔

Features	
Auto-restart	✔
Ports & interfaces	
USB port	✔
USB port type	USB Type-B
Ethernet LAN (RJ-45) ports	2
Cabling technology	10/100Base-T
Design	
Form factor *	Rackmount
Rack capacity	3U
Product colour *	Black
Display type	LCD

0731304322023

731304322023

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date