APC Power Cord Kit (6 ea), Locking, C19 to C20 (90 Degree), 1.2m



Brand : APC

Product code: AP8714R

Product name : Power Cord Kit (6 ea), Locking, C19 to C20 (90 Degree), 1.2m

- Locking IEC receptacle to reduce risk of accidental disconnections
- Universal fit in any IEC receptacles
- Output jumpers in multiple lengths and configurations
- Exclusive locking feature for APC AP8000 range of Rack PDUs
- Multi region approved with regional input sockets

Power Cord Kit (6 ea), Locking, C19 to C20 (90 Degree), 1.2m

APC Power Cord Kit (6 ea), Locking, C19 to C20 (90 Degree), 1.2m:

This product AP8714R can free up space and secure power cords between rack-mount PDUs and attached IT equipment with the exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
APC Power Cord Kit (6 ea), Locking, C19 to C20 (90 Degree), 1.2m. Cable length: 1.22 m

Features	
Product colour *	Black, Yellow
Connector 1 gender *	Male
Connector 2 gender *	Female
Cable length *	1.22 m
Operational conditions	
Operating temperature (T-T)	0 - 75 °C
Storage temperature (T-T)	-25 - 75 °C
Operating relative humidity (H-H)	20 - 80%
Storage relative humidity (H-H)	20 - 80%
Operating altitude	0 - 3000 m


Operational conditions	
Non-operating altitude	0 - 15000 m
Weight & dimensions	
Weight	1.64 kg
Packaging data	
Package weight	1.64 kg
Logistics data	
Harmonized System (HS) code	84733080
Total carbon footprint (kg of CO2e)	515.93
Other features	
Output connections	IEC 320 C19
Input connection type	IEC-320 C20
Dimensions (WxDxH)	1651 x 70 x 300 mm



0731304279693



731304279693



7313042796934

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date