Brother LC980MBP ink cartridge 1 pc(s) Original Magenta



Brand : Brother

Product code: LC980MBP

Product name : LC980MBP

LC-980MBP - Magenta

Brother LC980MBP ink cartridge 1 pc(s) Original Magenta:

Brother original supplies maintain top quality results & offer great value for money.

Brother employ precision engineering in the development of ink. These inks are specially designed to give you high quality results from your Brother printing technology every time.

Brother original supplies produce images that are true to life, every time.

Brother's colour matching process is designed to work with Brother's own ink formula.

Low cost individual cartridges, just replace the empty colour cartridge reducing wastage and cost.
Brother LC980MBP. Colour ink type: Pigment-based ink, Supply type: Single pack, Colour ink page yield: 260 pages, Colour ink volume: 5.5 ml, Printing colours: Magenta, Quantity per pack: 1 pc(s)

Features	
Colour ink type	Pigment-based ink
Print technology	Inkjet printing
Compatibility *	DCP-145C DCP-165C DCP-195C DCP-197C DCP-375CW MFC-250C MFC-255CW MFC-290C MFC-295C
Quantity per pack *	1 pc(s)
Colour ink volume	5.5 ml
Colour ink page yield *	260 pages
Type *	Original
Ink type	Pigment-based ink
Printing colours *	Magenta
Brand compatibility *	Brother
Supply type *	Single pack
Country of origin	Malaysia
Weight & dimensions	
Width	40 mm
Depth	122 mm

Weight & dimensions	
Height	178 mm
Weight	37 g
Packaging data	
Package weight	65 g
Package type	Blister
Logistics data	
Pallet gross height	16.7 cm
Products per pallet	1680 pc(s)
Master (outer) cases per pallet	168 pc(s)
Layers per pallet	8 pc(s)
Master (outer) cases per pallet layer	21 pc(s)
Pallet gross weight	142.5 kg
Harmonized System (HS) code	84439990
Pallet type	1200 x 1000 mm

5014047560903

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date