APC NetShelter Cable Management, Vertical Cable Manager, Cable Rings, Set of 8, Black, 55 mm x 766 mm x 85 mm

Brand : APC

Product code: AR8442

Product name : APC NetShelter Cable Management, Vertical Cable Manager, Cable Rings, Set of 8, Black, 55 mm x 766 mm x 85 mm

APC NetShelter Cable Management, Vertical Cable Manager, Cable Rings, Set of 8, Black, 55 mm x 766 mm x 85 mm

APC NetShelter Cable Management, Vertical Cable Manager, Cable Rings, Set of 8, Black, 55 mm x 766 mm x 85 mm:


This product AR8442 occupies one bay of rear Zero U channel.
APC NetShelter Cable Management, Vertical Cable Manager, Cable Rings, Set of 8, Black, 55 mm x 766 mm x 85 mm. Type: Cable management panel, Product colour: Black. Weight: 1.82 kg

Features	
Type *	Cable management panel
Product colour *	Black
Built-in fan	✕
On/off switch	✕
Castor wheels	✕
Locking	✕
Certification	REACH
Weight & dimensions	
Width	55 mm
Depth (max)	8.5 cm
Height	766 mm

Weight & dimensions	
Weight	1.82 kg
Packaging data	
Package width	64 mm
Package depth	140 mm
Package height	832 mm
Package weight	2.09 kg
Technical details	
Total carbon footprint (kg of CO2e)	6.34
Compliance certificates	RoHS
Logistics data	
Harmonized System (HS) code	85389099




5051749236248



0731304222590



731304222590



0132017768502




132017768502




0168141583575




168141583575



7313042225908




4053162379329



0777787388712



777787388712



0971478541206



971478541206



5054484091349



0611101427285




611101427285



0804904214194



804904214194




5052461188556



0172302772043




172302772043




0132017633954




132017633954



5054629066249



0151903012222



151903012222



0531479661527



531479661527



5054533091344

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date