Epson Turtle T1575 Light Cyan



Brand : Epson **Product family:** Turtle **Product code:** C13T15754010

Product name : T1575 Light Cyan

- Excellent colour stability
- Exceptional light-fastness
- Excellent black and white image quality with three levels of black

T1575 Light Cyan

Epson Turtle T1575 Light Cyan:

Epson UltraChrome K3 inks are well known for their wide gamut and accurate colour rendition with virtually no colour twist. Now, with the addition of newly formulated vivid magenta and vivid light magenta inks, they offer an even wider colour gamut with a dramatically improved range of expression. Epson Turtle T1575 Light Cyan. Colour ink type: Pigment-based ink, Cartridge capacity: High (XL) Yield, Colour ink page yield: 2300 pages, Colour ink volume: 25.9 ml, Printing colours: Light Cyan, Quantity per pack: 1 pc(s)

Features	
Colour ink type	Pigment-based ink
Print technology	Inkjet printing
Compatibility *	- Epson Stylus Photo R3000
Quantity per pack *	1 pc(s)
Colour ink cartridges quantity	1
Colour ink volume	25.9 ml
Colour ink page yield *	2300 pages
Type *	Original
Cartridge capacity	High (XL) Yield
Ink type	Pigment-based ink
Printing colours *	Light Cyan
Brand compatibility *	Epson
OEM code	C13T15754010
Country of origin	China
Colour	✔

Operational conditions	
Storage temperature (T-T)	-20 - 40 °C

Packaging data	
Package width	145 mm
Package depth	33 mm
Package height	120 mm
Package type	Blister

Other features	
Certification	CE

Logistics data	
Pallet gross width	80 cm
Pallet gross length	120 cm
Pallet gross height	48 cm
Products per pallet	2400 pc(s)
Harmonized System (HS) code	84439990
Pallet width (UK)	100 cm
Pallet length (UK)	120 cm
Pallet height (UK)	48 cm
Products per pallet (UK)	2400 pc(s)
Products per pallet layer	240 pc(s)
Products per pallet layer (UK)	240 pc(s)
Minimum order quantity	8 pc(s)



3610170034988



4052305771518



8715946479477



4053162273740




5053676863382




5052217525994



5082014032043



8411121125282



8411300213465



8411100252671



5054230269190



5054484337157

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date



5054629238646



5053106096588



8715946487991



5054533337152



4053617033653

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date