



TP-Link Power over Ethernet Adapter Kit

Brand : TP-Link **Product code:** TL-POE200 V1

Product name : Power over Ethernet Adapter Kit

- Carries power & data over a single Ethernet cable up to 100 meters away
 - Selectable power output
 - Plug-and-Play, requires no configuration
- PoE Adapter Kit, IEEE 802.3, 802.3u, RJ-45, Silver/grey
- TP-Link Power over Ethernet Adapter Kit. Ethernet interface type: Gigabit Ethernet, Ethernet LAN data rates: 10,100,1000 Mbit/s. Product colour: Grey, Silver, Maximum operating distance: 100 m. Power over Ethernet (PoE) voltage: 12 V, Power requirements: 100 - 240VAC, AC adapter input voltage: 100 - 240 V. Compliance industry standards: IEEE802.3, IEEE802.3u. Width: 80.8 mm, Depth: 54 mm, Height: 24 mm



Network		Operational conditions	
Ethernet interface type	Gigabit Ethernet	Operating temperature (T-T)	0 - 40 °C
Ethernet LAN data rates	10,100,1000 Mbit/s	Operating relative humidity (H-H)	10 - 90%
Power over Ethernet (PoE)	✓	Storage temperature (T-T)	-40 - 70 °C
Auto MDI/MDI-X	✓	Storage relative humidity (H-H)	10 - 90%
Features		Weight & dimensions	
Product colour	Grey, Silver	Width	80.8 mm
Plug and Play	✓	Depth	54 mm
Maximum operating distance	100 m	Height	24 mm
Power		Packaging content	
Power over Ethernet (PoE) voltage *	12 V	Number of products included	2 pc(s)
Power requirements	100 - 240VAC	Packaging data	
AC adapter input voltage	100 - 240 V	Package width	198 mm
Input voltage	48 V	Package depth	165 mm
Input current	0.5 A	Package height	65 mm
Certificates		Package weight	430 g
Compliance industry standards	IEEE802.3, IEEE802.3u	Package type	Box



0845973030551



845973030551



6935364030551

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.