Brother TN-3380 toner cartridge 1 pc(s) Original Black

Brand : Brother

Product code: TN-3380

Product name : TN-3380



- Prints 8,000 pages in accordance with ISO/IEC19752
- High quality genuine Brother cartridge
- Prevents waste to save you paper, time and money

The Brother TN3380 Black Toner Cartridge. Prints 8,000 pages.

Brother TN-3380 toner cartridge 1 pc(s) Original Black:

As it’s the standard colour of many print jobs, you may find that you need to replenish your black cartridge more often. This genuine Brother TN3380 High Yield Toner Cartridge is capable of printing up to 8,000 pages, producing brilliant results from the very first to the last page you print.
Brother TN-3380. Black toner page yield: 8000 pages, Printing colours: Black, Quantity per pack: 1 pc(s)



Features	
Compatibility *	DCP-8110, 8150, 8155, 8250, HL-5440, 5450, 5470, 6180, MFC-8510, 8520, 8710, 8950
Quantity per pack *	1 pc(s)
Black toner page yield *	8000 pages
Type *	Original
Printing colours *	Black
Cartridge return & recycling	✔
Country of origin	Vietnam

Weight & dimensions	
Width	201 mm
Depth	149 mm
Height	362 mm
Weight	722 g
Dimensions (WxDxH)	290 x 132 x 81 mm

Packaging data	
Package dimensions (WxDxH)	362 x 201 x 149 mm
Package weight	1.24 kg

Other features	
Print technology	Laser printing

Logistics data	
Harmonized System (HS) code	84439990
Master (outer) cases per pallet layer	5 pc(s)
Master (outer) cases per pallet	50 pc(s)
Layers per pallet	10 pc(s)
Products per pallet	150 pc(s)
Pallet gross height	18.4 cm
Pallet gross weight	178 kg
Pallet type	1200 x 1000 mm

4977766708906

4977766705707

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date