

Targus Privacy Screen 14.1"W 35.8 cm (14.1")

Brand : Targus

Product code: ASF141WEU

Product name : Privacy Screen 14.1"W



- Privacy Screen for laptop or desktop screens 14.1"W (16:10)
 - Works with touch screens and dual screens
 - Blue light filter: Targus Privacy Screens reduce blue light for better protection and reading comfort
 - Anti-glare
 - Protect the information on your screen from unwanted viewing
 - Targus privacy screens are more touch-sensitive than other screens on the market
 - Reversible screen: shiny side ensures clarity for viewing inside, matt side reduces glare for viewing outside or in a bright room
 - Three easy attachment options: under-bezel tabs, tab guides or re-usable adhesive strips
- Privacy Screen 14.1"W (16:10), 42g, transparent / black
- Targus Privacy Screen 14.1"W. Maximum screen size: 35.8 cm (14.1"). Protection features: Scratch resistant. Weight: 40 g

Design		Packaging data	
Maximum screen size *	35.8 cm (14.1")	Package depth	370 mm
Product colour	Black, Transparent	Package height	265 mm
Features		Package weight	190 g
Protection features	Scratch resistant	Packaging content	
Cleaning cloth	✓	Quick start guide	✓
Easy to apply	✓	Logistics data	
Easy to remove	✓	Quantity per pack	1 pc(s)
Brand compatibility	Any brand	Harmonized System (HS) code	84733080
Weight & dimensions		Products per pallet	2160 pc(s)
Width	1 mm	Master (outer) case width	60 mm
Height	190 mm	Master (outer) case length	390 mm
Depth	300 mm	Master (outer) case height	290 mm
Weight	40 g	Master (outer) case gross weight	2.15 kg
Packaging data		Products per master (outer) case	10 pc(s)
Package width	2 mm		

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date