Epson Bond Paper White 80, 914mm x 50m

Brand : Epson

Product code: C13S045275

Product name : Bond Paper White 80, 914mm x 50m



Bond Paper White 80, 914mm x 50m

Epson Bond Paper White 80, 914mm x 50m:

This paper is ideal for everyday plotting, technical drawings and illustrations. It shows crisp lines, high-contrast colour and sharp-looking characters from 1mm in size upwards, and is suitable for both dye and pigment inks.

- CAD paper ideal for everyday plotting
- Shows sharp lines and high-contrast colour
- Works well with dye and pigment ink
- Suitable for 100-year archival
- Meets ISO 9706 standard

Epson Bond Paper White 80, 914mm x 50m. Finish type: Matte, Media weight: 80 g/m², Product colour: White. Roll width: 91.4 cm, Roll length: 50 m. Quantity per pack: 1 pc(s), Package width: 105 mm, Package depth: 935 mm. Pallet gross width: 80 cm, Pallet gross length: 120 cm, Pallet gross height: 111 cm. Country of origin: China

Features	
Product colour	White
Finish type *	Matte
Media weight *	80 g/m²
Certification	ISO 9706
Compatible products	- SureColor SC-T7200D-PS - SureColor SC-T7200D - SureColor SC-T7200-PS - SureColor SC-T7200 - SureColor SC-P20000 - Epson SureColor SC-T7000 - Epson Stylus Pro 9890 SpectroProofer UV - Epson Stylus Pro 9890 SpectroProofer - Epson Stylus Pro 9890 - Epson Stylus Pro 9700 - Epson Stylus Pro 11880
Weight & dimensions	
Roll width	91.4 cm
Roll length	50 m

Packaging data	
Quantity per pack	1 pc(s)
Package width	105 mm
Package depth	935 mm
Package height	105 mm
Package weight	4.1 kg
Logistics data	
Harmonized System (HS) code	37032000
Pallet gross width	80 cm
Pallet gross length	120 cm
Pallet gross height	111 cm
Products per pallet	60 pc(s)
Products per pallet layer	60 pc(s)
Minimum order quantity	4 pc(s)
Other features	
Country of origin	China

8715946491127

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date