Brother LC221C ink cartridge 1 pc(s) Original Cyan



Brand : Brother

Product code: LC221C

Product name : LC221C

- Prints 260 pages in accordance with ISO/IEC 24711
- High quality genuine Brother cartridge
- Prevents waste to save you paper, time and money
- Using this Brother LC221C original ink cartridge protects your printer warranty
- The LC221 range of ink cartridges are available as a more economical value pack, reducing your cost per page - LC221VALBP

The Brother LC221C Cyan Ink Cartridge – Single Pack. Prints 260 pages.



Brother LC221C ink cartridge 1 pc(s) Original Cyan:

Specially designed to enable the high-quality printing of all your documents, you can rely on the LC221C to deliver professional results every time you print. With crisp prints from the first page to the last, this cyan ink cartridge is perfect for use at home or in the office.
Brother LC221C. Supply type: Single pack, Colour ink page yield: 260 pages, Printing colours: Cyan, Quantity per pack: 1 pc(s)

Features	
Print technology	Inkjet printing
Compatibility *	Brother DCP-J562DW, MFC-J480DW, MFC-J680DW, MFC-J880DW
Quantity per pack *	1 pc(s)
Colour ink page yield *	260 pages
Type *	Original
Printing colours *	Cyan
Brand compatibility *	Brother
Supply type *	Single pack
Country of origin	Philippines
Weight & dimensions	
Width	24 mm
Depth	116 mm
Height	91 mm
Weight	33 g

Packaging data	
Package weight	67 g
Other features	
Page yield footnote	ISO/IEC 24711
Paper dimensions	A4
Logistics data	
Pallet gross height	15.1 cm
Products per pallet	3000 pc(s)
Master (outer) cases per pallet	30 pc(s)
Layers per pallet	5 pc(s)
Master (outer) cases per pallet layer	6 pc(s)
Pallet gross weight	213 kg
Harmonized System (HS) code	84439990
Pallet type	800 x 1200 mm

4977766747325

5715328103009

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date