



APC NetShelter WX AR112, 12U, 19inch patch cabinet, Wall mounting, Unassembled, 600MM deep

Brand : APC

Product code: AR112

Product name : APC NetShelter WX AR112, 12U, 19inch patch cabinet, Wall mounting, Unassembled, 600MM deep

- Suitable for wall mounting
- Unassembled
- 12U
- 19inch
- Wall cabinet
- Lockable


APC NetShelter WX AR112 - 12U, 19inch patch cabinet, Wall mounting, Unassembled, 600MM deep
APC NetShelter WX AR112, 12U, 19inch patch cabinet, Wall mounting, Unassembled, 600MM deep. Type: Wall mounted rack, Rack capacity: 12U, Maximum weight capacity: 90.7 kg. Weight: 18.3 kg. Product colour: Black



Features		Weight & dimensions	
Rack capacity *	12U	Height	620 mm
Type *	Wall mounted rack	Weight	18.3 kg
Maximum weight capacity *	90.7 kg	Mounting depth (max)	52.8 cm
Product colour	Black	Packaging data	
Material	Steel	Package width	688 mm
Front door construction	Perforated	Package depth	683 mm
Side panels included	✓	Package height	293 mm
Preassembled	✗	Package weight	23.1 kg
Certification	EIA-310-E	Technical details	
Weight & dimensions		Total carbon footprint (kg of CO2e)	70.18
Size (imperial)	48.3 cm (19")	Logistics data	
Width	600 mm	Harmonized System (HS) code	85381000
Depth	600 mm		



0731304317289



731304317289

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.