Lenovo 46M4004 power distribution unit (PDU) 12 AC outlet(s) 1U Black



Brand : Lenovo

Product code: 46M4004

Product name : 46M4004

1U 12 C13 Switched and Monitored DPI PDU

Lenovo 46M4004 power distribution unit (PDU) 12 AC outlet(s) 1U Black:

The 1U Switched and Monitored Power Distribution Units (PDUs) make it quick and simple to deploy, protect, and manage your high-availability rack environment. These space efficient and power dense PDUs come in two unique 1U designs, either nine IEC-320-C19 (16A) and three IEC-320-C13 (10A) or 12 IEC-320-C13 (10A), with single-phase 30A, 32A, 60A, 63A and three-phase 32A and 60A solutions available to meet the requirements of your most power-demanding systems.
Lenovo 46M4004. PDU types: Monitored, Switched, Rack capacity: 1U, Type: Three-phase. AC outlets quantity: 12 AC outlet(s), AC outlet types: C13 coupler. Nominal input voltage: 200 - 240 V, AC input frequency: 50 - 60 Hz. Width: 447 mm, Depth: 350 mm, Height: 43.9 mm

Design	
PDU types *	Monitored, Switched
Type	Three-phase
Rack capacity *	1U
Product colour	Black
Ports & interfaces	
AC outlets quantity *	12 AC outlet(s)
AC outlet types *	C13 coupler

Power	
Nominal input voltage *	200 - 240 V
AC input frequency	50 - 60 Hz
Operational conditions	
Operating temperature (T-T)	10 - 60 °C
Weight & dimensions	
Width	447 mm
Depth	350 mm
Height	43.9 mm

0883436047876

883436047876

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date