

Epson Singlepack Magenta T614300 220 ml

Brand : Epson

Product code: C13T614300

Product name : Singlepack Magenta T614300 220 ml

Singlepack Magenta T614300 220 ml

Epson Singlepack Magenta T614300 220 ml:

The objective in developing the UltraChrome pigment ink was to combine the long-term and short-term colour stability properties of pigment inks with the colour scale of dye inks. This new colour ink system includes light black as seventh colour, which makes it possible to achieve softer gradations in the case of black&white printing, as well as two types of black ink, matt & photo, ensuring that optimal quality can be achieved on all media types.

Epson Singlepack Magenta T614300 220 ml. Colour ink type: Pigment-based ink, Colour ink volume: 220 ml, Printing colours: Magenta, Quantity per pack: 1 pc(s)



Features		Packaging data	
Colour ink type	Pigment-based ink	Package weight	0.426 g
Print technology	Inkjet printing	Logistics data	
Compatibility *	Stylus Pro 9600 / Pro 4000 / C4 / C8 / C8PS / 4400 / 4450	Pallet gross width	80 cm
Quantity per pack *	1 pc(s)	Pallet gross length	120 cm
Colour ink cartridges quantity	1	Pallet gross height	198 cm
Colour ink volume	220 ml	Products per pallet	1200 pc(s)
Type *	Original	Master (outer) case width	302 mm
Ink type	Pigment-based ink	Master (outer) case length	452 mm
Printing colours *	Magenta	Master (outer) case height	198 mm
Brand compatibility *	Epson	Products per master (outer) case	24 pc(s)
OEM code	C13T614300	Harmonized System (HS) code	84439990
Country of origin	China	Pallet width (UK)	100 cm
Packaging data		Pallet length (UK)	120 cm
Package width	27 mm	Pallet height (UK)	198 cm
Package depth	292 mm	Products per pallet (UK)	1680 pc(s)
Package height	110 mm	Products per pallet layer	120 pc(s)
		Products per pallet layer (UK)	168 pc(s)



0010343865990



010343865990

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.