

Epson LX-1350 dot matrix printer 240 x 144 DPI Colour

Brand : Epson

Product code: C11CD24301A0

Product name : LX-1350



Impact dot matrix, 9 pins, 136 columns, 9 Needles, 240 x 144 DPI, USB 2.0, RS-232, 33 Watt, 6.6 kg
Epson LX-1350. Maximum resolution: 240 x 144 DPI. Continuous paper thickness range: 0.065 - 0.39 mm. Product colour: Black, Buffer size: 128 KB, Sound pressure level (printing): 54 dB. Standard interfaces: RS-232, USB 2.0. Print head: 9-pin, Print head life: 400 million characters

Printing		Operational conditions	
Maximum resolution *	240 x 144 DPI	Operating relative humidity (H-H)	10 - 80%
Maximum printing width (columns) *	138	Storage relative humidity (H-H)	10 - 80%
Colour *	✓	Weight & dimensions	
Paper handling		Width	546 mm
Continuous paper thickness range	0.065 - 0.39 mm	Depth	275 mm
Features		Height	164 mm
Product colour *	Black	Weight	6.6 kg
Buffer size *	128 KB	Packaging data	
Sound pressure level (printing) *	54 dB	Quantity per pack	1 pc(s)
Country of origin	Indonesia	Package width	380 mm
Ports & interfaces		Package depth	640 mm
Standard interfaces *	RS-232, USB 2.0	Package height	220 mm
Endurance		Package weight	7.73 kg
Print head *	9-pin	Logistics data	
Print head life	400 million characters	Products per pallet	27 pc(s)
Power		Pallet gross length	120 cm
Power consumption (typical)	33 W	Pallet gross width	80 cm
AC input voltage	220 - 240 V	Pallet gross height	2.15 m
Operational conditions		Products per pallet layer	3 pc(s)
Operating temperature (T-T)	5 - 35 °C	Products per pallet layer (UK)	3 pc(s)
Storage temperature (T-T)	5 - 35 °C	Products per pallet (UK)	27 pc(s)
		Pallet length (UK)	120 cm
		Pallet width (UK)	100 cm
		Pallet height (UK)	2.15 m



8715946540573

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.