

StarTech.com USB to 5.5mm Power Cable - Type M Barrel - 2m

Brand : StarTech.com

Product code: USB2TYPEM2M

Product name : USB to 5.5mm Power Cable - Type M Barrel - 2m

StarTech.com 2m USB to Type M Barrel Cable - USB to 5.5mm 5V DC Cable - USB to Barrel Jack 5V DC Plug (USB2TYPEM2M)

StarTech.com USB to 5.5mm Power Cable - Type M Barrel - 2m:

Power your 5V DC devices from your computer through a USB port

Tired of having to carry around a separate wall adapter in order to power or charge your 5V devices, such as certain external hard drives, streaming media players, and Bluetooth® speakers?

This 2m USB power cable makes it easier to power 5V DC devices that have a Type M (OD: 5.5mm, ID:2.1mm) barrel power connector. You can power or charge the devices through an available USB port on your laptop or desktop computer.

Expertly designed and constructed of high-quality materials, the StarTech.com USB2TYPEM2M power cable is backed by our lifetime warranty.

The StarTech.com Advantage

StarTech.com USB to 5.5mm Power Cable - Type M Barrel - 2m. Cable length: 2 m, Connector 1: USB, Connector 2: Barrel type M



Features		Weight & dimensions	
Product colour *	Black	Width	15 mm
Connector 1 gender *	Male	Depth	2000 mm
Connector 2 gender *	Male	Height	10 mm
Cable length *	2 m	Weight	49 g
Connector 1 *	USB	Packaging data	
Connector 2 *	Barrel type M	Package width	125 mm
Connector 1 form factor	Straight	Package depth	225 mm
Connector 2 form factor	Straight	Package height	12 mm
Connector contacts plating	Nickel	Package weight	54 g
Jacket material	Polyvinyl chloride (PVC)	Logistics data	
AWG wire size	28	Harmonized System (HS) code	84733080
Cable shielding	Aluminum mylar foil	Master (outer) case width	345 mm
Certificates		Master (outer) case length	390 mm
Compliance certificates	RoHS	Master (outer) case height	310 mm
Certification	CE, REACH	Products per master (outer) case	200 pc(s)



0065030848374



065030848374



5055851123748



0728956306389



728956306389

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.