Lenovo AUKP Internal Ethernet 10000 Mbit/s



Brand : Lenovo

Product code: 7ZT7A00496

Product name : AUKP

ThinkSystem Broadcom NX-E PCIe, 10Gb, 2-Port Base-T Ethernet Adapter
Lenovo AUKP. Internal. Connectivity technology: Wired, Host interface: PCI Express, Interface: Ethernet. Maximum data transfer rate: 10000 Mbit/s. Product colour: Black, Green

Ports & interfaces	
Connectivity technology *	Wired
Host interface *	PCI Express
Interface *	Ethernet
Ethernet LAN (RJ-45) ports	2

Network	
Maximum data transfer rate *	10000 Mbit/s
Networking standards *	IEEE 802.3ab, IEEE 802.3an
Ethernet LAN data rates	10,100,1000,10000 Mbit/s
Cabling technology	10GBase-T
Jumbo frames support	✔
iSCSI support	✔
Maximum operating distance	100 m

Design	
Product colour	Black, Green
Internal *	✔

Design	
Certification	CE/European Union EN60950-1 UL/USA UL60950-1 CTUVus UL Canada: CSA 22.2 No. 950 Taiwan: CNS14336 Class A EN55022:2010 + *AC:2011 Class A EN55024 Class A FCC CFR47, Part 15 Class A Canada: ICES-003 Class A Australia, New Zealand: EN 5022:2010 + *AC:2011 Taiwan: BSMI CNS13438 Class A South Korea: MIC RRL KN22 Class A South Korea: KN24 (ESD) Japan: VCCI V-3 04/2014 EN55024:2010 Air/Direct discharge

Operational conditions	
Storage temperature (T-T)	-40 - 65 °C
Operating relative humidity (H-H)	5 - 95%
Storage relative humidity (H-H)	5 - 95%

Weight & dimensions	
Width	69 mm
Depth	168 mm
Height	15 mm

Logistics data	
Harmonized System (HS) code	85176990

0889488433612

889488433612

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date