



DELL 540-BBUO network card Internal 10000 Mbit/s

Brand : DELL

Product code: 540-BBUO

Product name : 540-BBUO

- Features a compact space-saving design
 - Ideal for high-performance network applications
- Broadcom 57416 Dual Port 10Gb Base-T PCIe Adapter Full Height Customer Install

DELL 540-BBUO network card Internal 10000 Mbit/s:

The Broadcom 57416 10Gb Base-T, Network Interface Card from Dell™ is ideal for connecting your server to your network. The Dual Port PCIe Adapter proven to be reliable and standards-based solutions. This product has been tested and validated on Dell systems. It is supported by Dell Technical Support when used with a Dell system.

This product is compatible with the following systems:

- PowerEdge R640
- PowerEdge R740
- PowerEdge R740XD
- PowerEdge R940
- PowerEdge T640
- PowerEdge T440
- PowerEdge R440
- PowerEdge R540
- PowerEdge R7415
- PowerEdge R7425
- PowerEdge R840
- PowerEdge R940xa
- PowerVault NX3240
- PowerEdge R340
- PowerEdge R740xd2
- PowerEdge XR2
- PowerEdge R6525
- PowerEdge R7515
- PowerEdge R7525

Ports & interfaces		Design	
Connectivity technology *	Wired	Component for *	Server
Host interface *	PCI Express	Internal *	✓
PCI Card form factor	Full-height		- PowerEdge R440 - PowerEdge R540 - PowerEdge R640 - PowerEdge R740 - PowerEdge R740XD - PowerEdge R940 - PowerEdge T440 - PowerEdge T640
Network		Compatible products	
Maximum data transfer rate *	10000 Mbit/s		
Cabling technology	10GBase-T		
Data link protocols	10 GigE		
Logistics data			
		Harmonized System (HS) code	85176990



5397184035337



5711783922650



0884116329268



884116329268

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.