APC Battery Replacement Cartridge APCRBC114 (OEM)

Brand : APC

Product code: APCRBC114

Product name : Battery Replacement Cartridge APCRBC114 (OEM)



- 12V 4.3AH replaceable battery for APC Back-UPS
- Brand new battery shipped from strictly managed warehouse
- Peace of mind with 2-year warranty and UPS safety certifications
- Supports APC-authorized recycling for earth-friendly disposal
- lead-acid battery

Battery Replacement Cartridge APCRBC114 (OEM)

APC Battery Replacement Cartridge APCRBC114 (OEM):

The genuine APC Replacement Battery Cartridge (RBC) is tested and certified for 100% compatibility to the the specific APC UPS. This lead-acid RBC has a lifetime of three to five years which offers reliable support and extends the useful life of your UPS. The APC RBC comes fully assembled and ready for use. To see the compatible UPS list, please click View Compatible UPS Modelsbutton in Get Support Section at APC.com

Features	
Battery technology *	Sealed Lead Acid (VRLA)
Battery voltage *	12 V
Battery capacity	60 VAh
Number of batteries included *	1 pc(s)
Battery life	5 year(s)
Product colour	Black
Certificates	
Compliance certificates	RoHS
Weight & dimensions	
Weight	1.45 kg
Width	53 mm
Height	100 mm
Depth	153 mm
Packaging data	
Package width	85 mm

Packaging data	
Package height	178 mm
Package depth	210 mm
Package weight	1.7 kg
Operational conditions	
Operating temperature (T-T)	0 - 40 °C
Storage temperature (T-T)	-5 - 45 °C
Operating relative humidity (H-H)	0 - 95%
Storage relative humidity (H-H)	0 - 95%
Operating altitude	0 - 3000 m
Non-operating altitude	0 - 15000 m
Logistics data	
Harmonized System (HS) code	85044095
Total carbon footprint (kg of CO2e)	5.51

0731304264385

731304264385

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date