APC NetShelter Basic Rack PDU, Zero U, 12.5kW, 208V, 30 C13 and 6 C19 outlet, 3ft input Cord



Brand : APC

Product code: AP7568

Product name : APC NetShelter Basic Rack PDU, Zero U, 12.5kW, 208V, 30 C13 and 6 C19 outlet, 3ft input Cord

APC NetShelter Basic Rack PDU, Zero U, 12.5kW, 208V, 30 C13 and 6 C19 outlet, 3ft input Cord

APC NetShelter Basic Rack PDU, Zero U, 12.5kW, 208V, 30 C13 and 6 C19 outlet, 3ft input Cord:

-Includes: Cord retention bracket(s), Documentation CD, Installation guide, Rack Mounting brackets, Toolless Mounting Kit.
-Multi-branch power input.
-Toolless mounting capability.
-Vertical mounting capability.
APC NetShelter Basic Rack PDU, Zero U, 12.5kW, 208V, 30 C13 and 6 C19 outlet, 3ft input Cord. Product colour: Black. Input connection type: Hubbell CS8365C, Output connections: -(30) IEC 320 C13. -(6) IEC 320 C19. . Cable length: 0.91 m. Nominal input voltage: 208 V, Nominal output voltage: 208 V, Load capacity: 12500 VA. Certification: cUL,CSA C22.2 No. 60950-1-03,UL 60950-1,UL



Design	
Product colour	Black
Ports & interfaces	
Input connection type	Hubbell CS8365C
Output connections	-(30) IEC 320 C13. -(6) IEC 320 C19.
Features	
Cable length	0.91 m
Power	
Nominal input voltage *	208 V
Nominal output voltage	208 V
Load capacity	12500 VA
Maximum input current per phase	35 A
Maximum total current draw per phase	35 A

Certificates	
Certification	cUL,CSA C22.2 No. 60950-1-03,UL 60950-1,UL
Operational conditions	
Operating temperature (T-T)	-5 - 45 °C
Storage temperature (T-T)	-25 - 65 °C
Operating relative humidity (H-H)	5 - 95%
Storage relative humidity (H-H)	5 - 95%
Weight & dimensions	
Width	56 mm
Depth	89 mm
Height	1778 mm
Weight	6.95 kg



0731304226833



731304226833

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date