APC NetShelter AV, Server Rack Enclosure, 42U, 10-32 Threaded Rails, Black, 1991H x 600W x 825D mm



Brand : APC

Product code: AR3810

Product name : NetShelter AV, Server Rack Enclosure, 42U, 10-32 Threaded Rails, Black, 1991H x 600W x 825D mm

NetShelter AV, Server Rack Enclosure, 42U, 10-32 Threaded Rails, Black, 1991H x 600W x 825D mm

APC NetShelter AV, Server Rack Enclosure, 42U, 10-32 Threaded Rails, Black, 1991H x 600W x 825D mm:

Feature-rich enclosure specifically for the professional A/V market and optimized for cable management, power distribution, and airflow management
APC NetShelter AV, Server Rack Enclosure, 42U, 10-32 Threaded Rails, Black, 1991H x 600W x 825D mm. Type: Freestanding rack, Rack capacity: 42U, Maximum weight capacity: 1363640 kg. Weight: 119.5 kg. Product colour: Black

Features	
Rack capacity *	42U
Type *	Freestanding rack
Maximum weight capacity *	1363640 kg
Product colour	Black
Certification	UL 60950-1
Weight & dimensions	
Width	600 mm
Depth	825 mm
Height	1991 mm

Weight & dimensions	
Weight	119.5 kg
Packaging data	
Package weight	133.6 kg
Technical details	
Total carbon footprint (kg of CO2e)	405.5
Logistics data	
Harmonized System (HS) code	85381000
Other features	
Package dimensions (WxDxH)	749 x 1029 x 2121 mm



0731304281436



731304281436

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date