Epson Premium Matte Label - Continuous Roll: 102mm x 35m



Brand : Epson

Product code: C33S045419

Product name : Premium Matte Label - Continuous Roll: 102mm x 35m

Premium Matte Label - Continuous Roll: 102mm x 35m

Epson Premium Matte Label - Continuous Roll: 102mm x 35m:

The smooth, bright white surface with a matte finish, in combination with Epson DURABrite Ultra pigment inks, ensures fast drying, scratch, water and heat resistance. The universal permanent acrylic adhesive enables trouble-free performance and good adhesion on a variety of surfaces and also at low temperatures.

Suggested applications
• Barcode labels
• Box labels for consumer products
• Parts assembly labels
• Shelf-edge labels in retail
• Pharmaceutical labels
• Sample labels in healthcare
• Shipping labels
Epson Premium Matte Label - Continuous Roll: 102mm x 35m. Finish type: Matte, Print media weight: 163 g/m². Quantity per pack: 1 pc(s), Package width: 113 mm, Package depth: 108 mm. Products per pallet: 648 pc(s), Pallet gross length: 120 cm, Pallet gross width: 80 cm. Country of origin: Poland

Features	
Finish type	Matte
Print media weight	163 g/m²
Packaging data	
Quantity per pack	1 pc(s)
Package width	113 mm
Package depth	108 mm
Package height	113 mm
Package weight	636 g
Logistics data	
Products per pallet	648 pc(s)
Pallet gross length	120 cm
Pallet gross width	80 cm

Logistics data	
Pallet gross height	102 cm
Minimum order quantity	18 pc(s)
Products per pallet layer	216 pc(s)
Products per pallet layer (UK)	288 pc(s)
Products per pallet (UK)	864 pc(s)
Pallet length (UK)	120 cm
Pallet width (UK)	100 cm
Pallet height (UK)	102 cm
Harmonized System (HS) code	84439990
Other features	
Country of origin	Poland

8715946527062

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date