



Lenovo RT11kVA uninterruptible power supply (UPS) Double-conversion (Online) 11 kVA 10000 W 4 AC outlet(s)

Brand : Lenovo

Product code: 55949PX

Product name : RT11kVA



1000 VA, 10000 W, 6 U, 3:1, 200 - 250 V, 4 x C19, 50 - 60 Hz
Lenovo RT11kVA. UPS topology: Double-conversion (Online), Output power capacity: 11 kVA, Output power: 10000 W. AC outlet types: C19 coupler, AC outlets quantity: 4 AC outlet(s). Form factor: Tower, Product colour: Black, Rack capacity: 6U. Weight: 23 kg

Features		Ports & interfaces	
UPS topology *	Double-conversion (Online)	AC outlet types	C19 coupler
Output power capacity *	11 kVA	AC outlets quantity	4 AC outlet(s)
Output power *	10000 W	Design	
Input operation voltage (min) *	200 V	Form factor *	Tower
Input operation voltage (max) *	250 V	Rack capacity	6U
Input frequency *	50/60 Hz	Product colour *	Black
Number of input phases	3	Weight & dimensions	
Number of output phases	1	Weight	23 kg
		Logistics data	
		Harmonized System (HS) code	85078000



0883436548205



883436548205

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.