



# Canon PFI-1000PBK Photo Black Ink Cartridge

**Brand :** Canon **Product code:** 0546C001

**Product name :** PFI-1000PBK Photo Black Ink Cartridge



- Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges<sup>2</sup>
  - Genuine Canon Ink provides consistent quality prints 100% of the time<sup>2</sup>
  - Genuine Canon Ink is 100% reliable so you can print with less stress<sup>2</sup>
  - Return every ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.
- PFI-1000PBK Photo Black Ink Cartridge

## Canon PFI-1000PBK Photo Black Ink Cartridge:

Bring your images to life with the LUCIA PRO ink range of professional inks for detailed and reliable results. This pigment-based ink system delivers a variety of deep, rich colours and sets your prints apart with outstanding photo permanence. The 80ml photo black ink tank allows you to print up to 2205 photos in 10x15cm or 256 in A2 size at ISO/IEC 29103<sup>1</sup> standard.

Canon PFI-1000PBK Photo Black Ink Cartridge. Colour ink type: Dye-based ink, Black ink volume: 80 ml, Printing colours: Photo black, Black ink page yield: 2205 pages

| Features               |                       | Features                    |             |
|------------------------|-----------------------|-----------------------------|-------------|
| Colour ink type        | Dye-based ink         | Printing colours *          | Photo black |
| Print technology       | Inkjet printing       | Brand compatibility *       | Canon       |
| Compatibility *        | imagePROGRAF PRO-1000 | Country of origin           | Japan       |
| Black ink volume       | 80 ml                 | Other features              |             |
| Black ink page yield * | 2205 pages            | Volume                      | 80 ml       |
| Type *                 | Original              | Logistics data              |             |
| Ink type               | Dye-based ink         | Harmonized System (HS) code | 84439990    |



4549292046342

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.