



Lenovo 44X1964 network transceiver module Fiber optic

Brand : Lenovo

Product code: 44X1964

Product name : 44X1964

8Gb/s optical transceiver module

Lenovo 44X1964 network transceiver module Fiber optic:

The IBM 44X1964 is a compact 8Gb/s optical transceiver module for serial optical communication applications at multi-rate of 2/4/8Gb/s. The IBM 44X1964 converts a 8Gb/s serial electrical data stream to 8Gb/s optical output signal and a 8Gb/s optical input signal to 8Gb/s serial electrical data streams. The high speed 8Gb/s electrical interface is fully compliant with SFI specification. The SPP5101SX-GL is designed for 8G Fiber Channel (8.5Gb/s) applications. The high performance 850nm VCSEL transmitter and high sensitivity PIN receiver provide superior performance for Ethernet applications at up to 150m links. The fully SFP compliant form factor provides hot pluggability, easy optical port upgrades and low EMI emission.

Lenovo 44X1964. SFP transceiver type: Fiber optic, Fiber optic connector: SFP

Performance		Logistics data	
SFP transceiver type *	Fiber optic	Harmonized System (HS) code	85176990
Fiber optic connector	SFP		





0883436048859



883436048859

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.