Epson WorkForce DS-50000 Flatbed scanner 600 x 600 DPI A3 White



Brand : Epson

Product code: B11B204131BY

Product name : WorkForce DS-50000

WorkForce DS-50000, 600 dpi x 600 dpi, ReadyScan LED, Monochrome: 4 s/page - Colour: 4 s/page, TWAIN, USB 2.0
Epson WorkForce DS-50000. Optical scanning resolution: 600 x 600 DPI, Input colour depth: 48 bit, Output colour depth: 24 bit. Scanner type: Flatbed scanner, Product colour: White, Display: LCD. Sensor type: CCD, Light source: ReadyScan LED, Scan file formats: JPG, PDF, TIFF. Maximum ISO A-series paper size: A3, Scanning media types supported: Plain paper, Thick paper, Thin paper, Transparencies, ISO A-series sizes (A0...A9): A3, A4, A5, A6. Optional connectivity: Ethernet, Standard interfaces: USB 2.0

Scanning	
Optical scanning resolution *	600 x 600 DPI
Colour scanning	✔
Duplex scanning *	✔
Input colour depth	48 bit
Output colour depth	24 bit
Film scanning	✘
Greyscale levels	256
ADF scan speed (b/w, A4)	15 ppm
ADF scan speed (colour, A4)	15 ppm
Flatbed scan speed (b/w, A4)	4 sec/page

Design	
Scanner type *	Flatbed scanner
Product colour *	White
Display	LCD
Built-in display *	✘

Performance	
Sensor type *	CCD
Light source	ReadyScan LED
Scan file formats	JPG, PDF, TIFF
Scan drivers	ISIS, TWAIN, WIA
Scanning noise level	54.9 dB

Paper handling	
Scanning media types supported	Plain paper, Thick paper, Thin paper, Transparencies
Maximum ISO A-series paper size *	A3
ISO A-series sizes (A0...A9)	A3, A4, A5, A6
ISO B-series sizes (B0...B9)	B5
Letter	✔
Legal	✔

Ports & interfaces	
USB port *	✔
USB version	2.0
Optional connectivity	Ethernet
Standard interfaces	USB 2.0

Network	
Ethernet LAN	✔

Power	
Power supply type *	AC

Weight & dimensions	
Width	640 mm
Depth	468 mm
Height	156 mm
Weight	14.8 kg

Packaging data	
Quantity per pack	1 pc(s)
Package width	635 mm
Package depth	844 mm
Package height	360 mm
Package weight	18.5 kg

Packaging content	
Drivers included	✔
Bundled software	ABBYY FineReader® Sprint 8.0 (MacOS), ABBYY FineReader® Sprint 9.0 (Windows), Epson Document Capture Pro (Windows only), Epson Document Capture Pro Server (on free download), Epson Event Manager (Mac Only), Epson Scan

Sustainability	
Sustainability certificates	ENERGY STAR

System requirements	
Windows operating systems supported	Windows 7 Home Basic, Windows 7 Home Basic x64, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows 8, Windows 8 Enterprise, Windows 8 Enterprise x64, Windows 8 Pro, Windows 8 Pro x64, Windows 8 x64, Windows Vista Business, Windows Vista Business x64, Windows Vista Enterprise, Windows Vista Enterprise x64, Windows Vista Home Basic, Windows Vista Home Basic x64, Windows Vista Home Premium, Windows Vista Home Premium x64, Windows Vista Ultimate, Windows Vista Ultimate x64, Windows XP Home, Windows XP Home x64, Windows XP Professional, Windows XP Professional x64

Power	
Power consumption (typical)	25.5 W
Power consumption (off)	1.5 W
Power consumption (PowerSave)	9.5 W
AC input frequency	50 - 60 Hz
Input voltage	100-240 V

System requirements	
Mac operating systems supported	✔

Operational conditions	
Operating temperature (T-T)	5 - 35 °C
Storage temperature (T-T)	-25 - 60 °C
Operating relative humidity (H-H)	10 - 80%
Storage relative humidity (H-H)	10 - 85%

Logistics data	
Products per pallet	5 pc(s)
Country of origin	China
Pallet gross length	120 cm
Pallet gross width	80 cm
Pallet gross height	162.5 cm
Products per pallet layer	1 pc(s)
Products per pallet layer (UK)	1 pc(s)
Products per pallet (UK)	5 pc(s)
Pallet length (UK)	120 cm
Pallet width (UK)	100 cm
Pallet height (UK)	162.5 cm
Harmonized System (HS) code	84716070

8715946510590

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date