

Brother LC22UBK ink cartridge 1 pc(s) Original High (XL) Yield Black

Brand : Brother

Product code: LC22UBK

Product name : LC22UBK

- Prints 2,400 pages in accordance with ISO/IEC 24711
 - High quality genuine Brother cartridge
 - Prevents waste to save you paper, time and money
- The Brother LC22UBK Black Ink Cartridge – Single Pack. Prints 2,400 pages.

Brother LC22UBK ink cartridge 1 pc(s) Original High (XL) Yield Black:

This genuine Brother LC22UBK Black Ink Cartridge has been specially developed to ensure quality documents every time you print. With colour fade resistant properties, you can enjoy sharp, crisp colours that last. By buying our cartridges, you protect your printer from potential long-term damage caused by using non-genuine products.

Brother LC22UBK. Cartridge capacity: High (XL) Yield, Black ink type: Pigment-based ink, Supply type: Single pack, Printing colours: Black, Quantity per pack: 1 pc(s), Black ink page yield: 2400 pages



Features		Weight & dimensions	
Black ink type	Pigment-based ink	Weight	96 g
Compatibility *	DCP-J785DW, MFC-J985DW	Packaging data	
Quantity per pack *	1 pc(s)	Package weight	142 g
Black ink cartridges quantity	1	Package type	Box
Black ink page yield *	2400 pages	Other features	
Type *	Original	Certification	ISO/IEC 24711
Cartridge capacity	High (XL) Yield	Logistics data	
Ink type	Pigment-based ink	Pallet gross height	14.8 cm
Printing colours *	Black	Products per pallet	1750 pc(s)
Brand compatibility *	Brother	Master (outer) cases per pallet	35 pc(s)
Supply type *	Single pack	Layers per pallet	5 pc(s)
Country of origin	Philippines	Master (outer) cases per pallet layer	7 pc(s)
Weight & dimensions		Pallet gross weight	266.5 kg
Width	40 mm	Harmonized System (HS) code	84439990
Depth	93 mm	Pallet type	800 x 1200 mm
Height	115 mm		



4977766759649



5715328103184

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.