

Epson EB-1795F Standard throw projector 3200 ANSI lumens 3LCD 1080p (1920x1080) Black, White



Brand : Epson

Product code: V11H796041

Product name : EB-1795F

3LCD, 3200Lm, 1920 x 1080, 16:9, 10000:1, 30 - 300", Lamp 214W, 4000h, 10bits, Manual zoom, Manual focus, MHL, NFC, Wireless LAN IEEE 802.11b/g/n, 39dB, 292 x 213 x 44mm, 1.8kg
 Epson EB-1795F. Projector brightness: 3200 ANSI lumens, Projection technology: 3LCD, Projector native resolution: 1080p (1920x1080). Light source type: Lamp, Service life of light source: 4000 h, Service life of light source (economic mode): 7000 h. Focus: Manual, Focal length range: 13.52 - 16.22 mm, Aperture range (F-F): 1.58 - 1.7. Supported graphics resolutions: 1920 x 1080 (HD 1080), Supported video modes: 1080p, Video processing: 10 bit. Wi-Fi standards: 802.11b, 802.11g, Wi-Fi 4 (802.11n)

Projector		Features	
Screen size compatibility *	762 - 7620 mm (30 - 300")	Air filter	✓
Projection distance (wide)	0.7 - 6.8 m	Country of origin	Philippines
Projection distance (tele)	0.8 - 8.2 m	Password protection	✓
Projector brightness *	3200 ANSI lumens	Multimedia	
Projection technology *	3LCD	Built-in speaker(s) *	✓
Projector native resolution *	1080p (1920x1080)	RMS rated power	1 W
Contrast ratio (typical) *	10000:1	Number of built-in speakers	1
Native aspect ratio *	16:9	Design	
Number of colours	1.073 billion colours	Product type *	Standard throw projector
Projector brightness (economic mode)	1900 ANSI lumens	Product colour *	Black, White
Vertical scan range	100 - 120 Hz	Placement	Desktop, Ceiling
Keystone correction, horizontal	-20 - 20°	Cable lock slot	✓
Keystone correction, vertical	-30 - 30°	Cable lock slot type	Kensington
Matrix size	1.5 cm (0.59")	Power	
Light source		Power source *	AC
Light source type *	Lamp	Power consumption (typical) *	295 W
Service life of light source *	4000 h	Power consumption (standby) *	0.34 W
Service life of light source (economic mode)	7000 h	Power consumption (economy mode)	208 W
Lamp power	214 W	AC input voltage	100 - 240 V
Lamps quantity	1 lamp(s)	AC input frequency	50 - 60 Hz
Lens system		Operational conditions	
Focus *	Manual	Operating temperature (T-T)	5 - 40 °C
Focal length range	13.52 - 16.22 mm	Storage temperature (T-T)	-10 - 60 °C
Aperture range (F-F)	1.58 - 1.7	Operating relative humidity (H-H)	20 - 80%
Zoom capability	✓	Storage relative humidity (H-H)	10 - 90%
Zoom type	Manual	Weight & dimensions	
Throw ratio	1.04 - 1.26:1	Width	292 mm
Video		Depth	213 mm
Full HD *	✓	Height	44 mm
3D *	✗	Weight *	1.8 kg
Supported graphics resolutions	1920 x 1080 (HD 1080)	Package width	370 mm
Supported video modes	1080p	Package depth	420 mm
Video processing	10 bit	Package height	145 mm
Video colour modes	Blackboard, Cinema, Dynamic, Presentation, sRGB	Package weight	3.73 kg
Ports & interfaces		Packaging content	
USB 2.0 ports quantity	2	Remote control included *	✓
PC in (D-Sub)	✓	Batteries included	✓
		Cables included	AC, VGA

Ports & interfaces		Packaging content	
VGA (D-Sub) ports quantity *	1	Carrying case	✓
HDMI ports quantity *	1	Technical details	
Composite video in *	1	Standard interfaces	HDMI, NFC, USB, VGA, Wireless LAN
DVI port *	✗	Logistics data	
Mobile High-Definition Link (MHL)	✓	Quantity per pack	1 pc(s)
Network		Products per pallet	70 pc(s)
Ethernet LAN *	✗	Pallet gross length	120 cm
Wi-Fi *	✓	Pallet gross width	80 cm
Wi-Fi standards	802.11b, 802.11g, Wi-Fi 4 (802.11n)	Pallet gross height	15 cm
Storage		Products per pallet layer	5 pc(s)
Card reader integrated *	✗	Products per pallet layer (UK)	6 pc(s)
Features		Products per pallet (UK)	84 pc(s)
Noise level (economic mode)	30 dB	Pallet length (UK)	120 cm
HDCP	✓	Pallet width (UK)	100 cm
Noise level *	39 dB	Pallet height (UK)	15 cm
		Harmonized System (HS) code	85286200



8715946629940

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.