Epson Padlock Singlepack Magenta 35XL DURABrite Ultra Ink

Brand : Epson **Product family:** Padlock **Product code:** C13T35934010

Product name : Singlepack Magenta 35XL DURABrite Ultra Ink

Singlepack Magenta 35XL DURABrite Ultra Ink
Epson Padlock Singlepack Magenta 35XL DURABrite Ultra Ink. Colour ink type: Pigment-based ink, Cartridge capacity: High (XL) Yield, Colour ink page yield: 1900 pages, Colour ink volume: 20.3 ml, Printing colours: Magenta, Quantity per pack: 1 pc(s)

Features	
Colour ink type	Pigment-based ink
Print technology	Inkjet printing
Compatibility *	- WorkForce Pro WF-4740DTWF - WorkForce Pro WF-4730DTWF - WorkForce Pro WF-4725DWF - WorkForce Pro WF-4720DWF
Quantity per pack *	1 pc(s)
Colour ink cartridges quantity	1
Colour ink volume	20.3 ml
Colour ink page yield *	1900 pages
Type *	Original
Cartridge capacity	High (XL) Yield
Ink type	Pigment-based ink
Printing colours *	Magenta
Brand compatibility *	Epson
OEM code	C13T35934010
Country of origin	Indonesia

Packaging data	
Package width	120 mm
Package depth	33 mm
Package height	145 mm
Package weight	72 g

Packaging data	
Package type	Blister

Other features	
Certification	CE

Logistics data	
Products per pallet	2400 pc(s)
Pallet gross weight	0 g
Master (outer) case width	120 mm
Master (outer) case length	260 mm
Master (outer) case height	146 mm
Products per master (outer) case	8 pc(s)
Master (outer) case gross weight	0 g
Master (outer) case GTIN (EAN/UPC)	8715946632834
Harmonized System (HS) code	84439990
Pallet weight (UK)	0 g
Products per pallet (UK)	2400 pc(s)
Products per pallet layer	240 pc(s)
Products per pallet layer (UK)	240 pc(s)
Minimum order quantity	8 pc(s)

8715946632391

4058154209219

5057454666929

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date