

StarTech.com 92x25mm Ball Bearing Quiet Computer Case Fan w/ TX3 Connector

Brand : StarTech.com

Product code: FAN9X25TX3L

Product name : 92x25mm Ball Bearing Quiet Computer Case Fan w/ TX3 Connector

StarTech.com 92x25mm Ball Bearing Quiet Computer Case Fan w/ TX3 Connector - 3 pin case Fan - TX3 Fan - 90mm Fan

[StarTech.com 92x25mm Ball Bearing Quiet Computer Case Fan w/ TX3 Connector:](#)

Add additional chassis cooling with a 92mm ball bearing fan

This quiet, dual ball-bearing (9.25cm) Case Fan offers a cost-effective solution for replacing a non-functional or noisy fan in your PC. Powered through a simple TX3 connection to the host computer power supply, the 8cm case fan helps keep your computer running at optimal temperatures for stable system performance.

The StarTech.com Advantage

- A dual ball bearing design ensures reliability and longer life
- A built-in tachometer allows for easy monitoring of the fan performance
- Backed by a StarTech.com 2-year warranty and free lifetime technical support

StarTech.com 92x25mm Ball Bearing Quiet Computer Case Fan w/ TX3 Connector. Type: Fan, Fan diameter: 9.2 cm, Rotational speed (max): 1800 RPM. Voltage: 12 V. Width: 25 mm, Depth: 92 mm, Height: 92 mm. Product colour: Black



Performance		Weight & dimensions	
Suitable location *	Computer case	Width	25 mm
Type *	Fan	Depth	92 mm
Fan diameter	9.2 cm	Height	92 mm
Rotational speed (max)	1800 RPM	Weight	108 g
Noise level (high speed)	22 dB	Package width	98 mm
Maximum airflow	31.84 cfm	Package depth	144 mm
Mean time between failures (MTBF)	50000 h	Package height	34 mm
Operating temperature (T-T)	-10 - 80 °C	Package weight	98 g
Design		Technical details	
Product colour *	Black	Bearing technology	Ball bearing
Material	Plastic	Compliance certificates	RoHS
Number of fans	1 fan(s)	Other features	
Power		Dimensions (WxDxH)	92 x 92 x 25 mm
Power consumption (typical)	1.08 W	Connector(s)	1 - TX3 Female
Voltage	12 V	Airflow	35.7
		Rotational speed	1600 RPM
Logistics data			
		Harmonized System (HS) code	84733080



0065030788953




065030788953



0151903683958



151903683958



5051964167006

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.