APC NBACS125 security access control system 0.125 MHz Black

Brand : APC **Product code:** NBACS125

Product name : NBACS125

125kHz, 1U, 432 x 59 x 44 mm, 1270 g

APC NBACS125 security access control system 0.125 MHz Black:

Network appliances enabling remote and local access control for your NetShelter SX enclosures.

APC Universal Sensors Supported:

Door contact
Dry Contact
Humidity
Smoke
Fluid Spot Leak
Temperature
Vibration
APC NBACS125. Operating frequency: 0.125 MHz, Product colour: Black, Chassis type: 1U. Dimensions (WxDxH): 614 x 246 x 304 mm. Width: 432 mm, Depth: 59 mm, Height: 44 mm. Package dimensions (WxDxH): 1937 x 904 x 529 mm, Package weight: 2.45 kg

Features	
Operating frequency	0.125 MHz
Product colour	Black
Chassis type	1U
Relative humidity	0 - 95%
Other features	
Dimensions (WxDxH)	614 x 246 x 304 mm
Operational conditions	
Operating temperature (T-T)	0 - 45 °C
Storage temperature (T-T)	0 - 95 °C

Operational conditions	
Operating relative humidity (H-H)	-15 - 65%
Weight & dimensions	
Width	432 mm
Depth	59 mm
Height	44 mm
Weight	1.27 kg
Packaging data	
Package dimensions (WxDxH)	1937 x 904 x 529 mm
Package weight	2.45 kg



0731304332077



731304332077



7612205027565



5415247160977



8592978126384



8592978053185



3606481978011



3015220883569



5054444037233

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date