



APC Smart-UPS On-Line SRT Battery Pack for 3kVA Extended runtime model 96V

Brand : APC

Product code: SRT96BP

Product name : Smart-UPS On-Line SRT Battery Pack for 3kVA Extended runtime model 96V

Smart-UPS On-Line SRT Battery Pack for 3kVA Extended runtime model 96V

APC Smart-UPS On-Line SRT Battery Pack for 3kVA Extended runtime model 96V:

This APC Smart-UPS battery pack connected with SRT On-Line UPS, provides extended runtime to SRT mission critical applications. This 96V SRT extendable runtime battery pack is compatible with 3kVA SRT Smart-UPS extended runtime models. Embedded monitoring at the cell, module, and cabinet level provides data of battery runtime and health. It is a lead-acid battery with a 2-year warranty. It is a lead-acid battery with a 2-year warranty. Its dimensions are 594mm (depth) x 432mm (height) x 85mm (width) and weighs 40.6kg. Ideal for Smart-UPS on-line mission critical applications. APC Smart-UPS On-Line SRT Battery Pack for 3kVA Extended runtime model 96V. Battery technology: Lead acid, Battery voltage: 96 V, Number of batteries included: 1 pc(s). Compliance certificates: RoHS. Weight: 40.6 kg, Width: 85 mm, Height: 432 mm. Package width: 599 mm, Package height: 239 mm, Package depth: 831 mm



Features		Packaging data	
Battery technology *	Lead acid	Package height	239 mm
Battery voltage *	96 V	Package depth	831 mm
Number of batteries included *	1 pc(s)	Package weight	44.5 kg
Product colour	Black	Operational conditions	
Hot-swap battery	✓	Operating temperature (T-T)	0 - 40 °C
Certificates		Storage temperature (T-T)	-15 - 45 °C
Compliance certificates	RoHS	Operating relative humidity (H-H)	0 - 95%
Weight & dimensions		Storage relative humidity (H-H)	0 - 95%
Weight	40.6 kg	Non-operating altitude	0 - 15000 m
Width	85 mm	Logistics data	
Height	432 mm	Harmonized System (HS) code	85044095
Depth	594 mm	Total carbon footprint (kg of CO2e)	203.76
Packaging data			
Package width	599 mm		



0731304317722



731304317722

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.