Brother LC121M ink cartridge 1 pc(s) Original Magenta



Brand : Brother

Product code: LC121M

Product name : LC121M

- Prints 300 pages in accordance with ISO/IEC 24711
- High quality genuine Brother cartridge
- Prevents waste to save you paper, time and money
- Using this Brother LC121M original ink cartridge protects your printer warranty
- The LC121 range of ink cartridges are available as a more economical value pack, reducing your cost per page - LC121VALBP

The Brother LC121M Magenta Ink Cartridge – Single Pack. Prints 300 pages.



Brother LC121M ink cartridge 1 pc(s) Original Magenta:

This replacement LC121M Ink Cartridge in Magenta has been designed to provide impressive results every time you print. As a genuine Brother supply, it's simple to install and guaranteed to be 100% compatible with your printer.
Brother LC121M. Colour ink type: Pigment-based ink, Supply type: Single pack, Colour ink page yield: 300 pages, Printing colours: Magenta, Quantity per pack: 1 pc(s)

Features	
Colour ink type	Pigment-based ink
Compatibility *	DCP-J752DW, MFC-J870DW
Quantity per pack *	1 pc(s)
Colour ink page yield *	300 pages
Type *	Original
Ink type	Pigment-based ink
Printing colours *	Magenta
Brand compatibility *	Brother
Supply type *	Single pack
Country of origin	Philippines

Operational conditions	
Operating relative humidity (H-H)	10 - 70%
Storage temperature (T-T)	10 - 35 °C
Operating temperature (T-T)	15 - 35 °C
Storage relative humidity (H-H)	5 - 95%

Weight & dimensions	
Width	85 mm
Depth	24 mm
Height	145 mm
Weight	34 g

Packaging data	
Package weight	67 g

Logistics data	
Pallet gross height	15 cm
Products per pallet	3000 pc(s)
Master (outer) cases per pallet	30 pc(s)
Layers per pallet	5 pc(s)
Master (outer) cases per pallet layer	6 pc(s)
Pallet gross weight	216 kg
Harmonized System (HS) code	84439990
Pallet type	800 x 1200 mm

4977766723206

5712505325841

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date