
3M Privacy Filter for 20in Monitor, 16:9, PF200W9B

Brand : 3M

Product code: 7000021449

Product name : Privacy Filter for 20in Monitor, 16:9, PF200W9B



- Effective "black out" privacy from side views outside the 60-degree viewing angle
- Durable privacy filter that can withstand hundreds of cleanings
- Helps reduce blue light, without distorting the natural color of your display.
- A reversible solution, 3M™ Privacy Filters offer a glossy option and a matte option that help reduce glare and fingerprints.
- 100% hand inspected for quality assurance.

Privacy Filter for 20in Monitor, 16:9, PF200W9B

3M Privacy Filter for 20in Monitor, 16:9, PF200W9B:

Achieve world-class privacy with 3M™ Privacy Filters, the leading name in screen solutions. Offers exceptional clarity and security while protecting screens from hazards without affecting performance. Make 3M your first line of defense against visual hackers, damage, glare, and more—at home, in the office, and everywhere you work.

Design	
Maximum screen size *	50.8 cm (20")
Suitable for *	Monitor
Type *	Frameless display privacy filter
Screen size HxW	443 x 250 mm
Display diagonal (metric)	50.8 cm
Filter colour	Black
Reversibility	Matte-to-Glossy
Product colour	Black

Features	
Display filter features *	Anti-glare
Display types supported *	LCD
Aspect ratio	16:9
Widescreen	✔
Scratch-resistant	✔
Protection features	Dust resistant, Scratch-resistant
Limits viewing angle	60°
Easy to clean	✔
Surface finish	Glossy / Matt
Screen format	Widescreen
Country of origin	United States
Easy to apply	✔
Durable screen protection	✔
Privacy filtering orientation	Landscape
Touchscreen compatible	✘
Installation type	Adhesive strip + Slide mount tab
Easy to remove	✔
Fingerprint resistant	✔
Blue light filter	✔

Weight & dimensions	
Width	443 mm
Height	250 mm
Weight	71 g

Packaging data	
Package width	470 mm
Package depth	5 mm
Package height	343 mm
Package weight	298 g

Other features	
Anti-reflective	✔
Special features	Compatible For Device With Raized Bezel
Compliance certificates	Trade Agreements Act (TAA)

Logistics data	
Pallet net height	121.9 cm
Pallet net length	121.9 cm
Pallet net width	106.7 cm
Pallet net weight	57.1 kg
Pallet weight (EU)	321.6 kg
Products per pallet (EU)	805 pc(s)
Harmonized System (HS) code	85299097
Pallet gross width	106.7 cm
Pallet gross length	121.9 cm
Pallet gross height	121.9 cm
Pallet gross weight	321.6 kg
Shipping (inner) case width	35.4 cm
Shipping (inner) case length	48.1 cm
Shipping (inner) case height	4.8 cm
Shipping (inner) case gross weight	1.9 kg
Shipping (inner) case net weight	355 g
Products per shipping (inner) case	5 pc(s)


Features		Logistics data	
Compatibility	HP W2082a; Dell E2011HT; HP Omni 120-1010a; Samsung LS20A300BS; Dell E2013; HP ProDisplay P203; Lenovo ThinkCentre M700z AiO; Lenovo ThinkVision L2021wA; LG Flatron E2042; ViewSonic VA2055Sm; HP EliteDisplay E202; LG Flatron E2041; HP EliteDisplay E201; Lenovo C340; HP Pavilion 20-b247la; Dell E2011HC; Dell P2011Ht; Dell XPS One A2010; HP ProDisplay P202; Samsung BX2035; Dell P2012Ht	Shipping (inner) case GTIN (EAN/UPC)	50051128789648



5052883396140



5147841649236



0804067413540



804067413540



0168141534690



168141534690




7427457535542



0163120266494




163120266494



0763615786935




763615786935



0777787389979

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date



777787389979



0808113028108




808113028108




0151903004111



151903004111



0640206629058




640206629058



0956260644297



956260644297



5052217497789




0767872165496



767872165496

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date



5711783915614



0132017618098




132017618098





5704174605508



0051128789643



051128789643

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date