
3M Privacy Filter for 24in Monitor, 16:10, PF240W1B

Brand : 3M

Product code: 7100026029

Product name : Privacy Filter for 24in Monitor, 16:10, PF240W1B



- Effective "black out" privacy from side views outside the 60-degree viewing angle
- Durable privacy filter that can withstand hundreds of cleanings
- Helps reduce blue light, without distorting the natural color of your display.
- A reversible solution, 3M™ Privacy Filters offer a glossy option and a matte option that help reduce glare and fingerprints.
- 100% hand inspected for quality assurance.

Privacy Filter for 24in Monitor, 16:10, PF240W1B

3M Privacy Filter for 24in Monitor, 16:10, PF240W1B:

Achieve world-class privacy with 3M™ Privacy Filters, the leading name in screen solutions. Offers exceptional clarity and security while protecting screens from hazards without affecting performance. Make 3M your first line of defense against visual hackers, damage, glare, and more—at home, in the office, and everywhere you work.

Design	
Maximum screen size *	61 cm (24")
Suitable for *	Monitor
Type *	Frameless display privacy filter
Screen size HxW	519 x 324 mm
Display resolution	1920 x 1200 pixels
Display diagonal (metric)	60.9 cm
Filter colour	Black
Reversibility	Matte-to-Glossy
Product colour	Black

Features	
Display filter features *	Anti-glare
Display types supported *	LCD
Aspect ratio	16:10
Widescreen	✔
Scratch-resistant	✔
Protection features	Dust resistant, Scratch-resistant
Limits viewing angle	60°
Easy to clean	✔
Surface finish	Glossy / Matt
Screen format	Widescreen
Country of origin	United States
Durable screen protection	✔
Privacy filtering orientation	Landscape
Touchscreen compatible	✘
Installation type	Adhesive strip + Slide mount tab
Easy to remove	✔
Fingerprint resistant	✔
Blue light filter	✔
Brand compatibility	HP
Compatibility	HP Compaq LA2405x

Weight & dimensions	
Height	324 mm
Weight	107 g

Packaging data	
Package width	552 mm
Package depth	5 mm
Package height	368 mm
Package weight	383 g


Other features	
Anti-reflective	✔
Special features	Compatible For Device With Raized Bezel
Compliance certificates	Trade Agreements Act (TAA)

Logistics data	
Pallet net height	121.9 cm
Pallet net length	121.9 cm
Pallet net width	106.7 cm
Pallet net weight	61.5 kg
Pallet weight (EU)	294.8 kg
Products per pallet (EU)	575 pc(s)
Harmonized System (HS) code	85299097
Pallet gross width	106.7 cm
Pallet gross length	121.9 cm
Pallet gross height	121.9 cm
Pallet gross weight	294.8 kg
Shipping (inner) case width	37.9 cm
Shipping (inner) case length	56.4 cm
Shipping (inner) case height	4.8 cm
Shipping (inner) case gross weight	2.42 kg
Shipping (inner) case net weight	535 g
Products per shipping (inner) case	5 pc(s)
Shipping (inner) case GTIN (EAN/UPC)	50051128787286

Weight & dimensions	
Width	519 mm



5712505738139




0803983050181



803983050181



5706998584397




0724627319351



724627319351




5052883395945



0640206699723




640206699723




0638084745076




638084745076



0151903015001




151903015001




0767872165533




767872165533



6768785932872



0809185305906




809185305906




0191120029115



191120029115




5147841649151



0999992878868



999992878868



5054184109870




4250251575291



0791836589929



791836589929




5053676749815




0809302059972



809302059972



5711783915676



5052461730601





5704174545842



0051128787281



051128787281

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date