

Epson Ultra Glossy Photo Paper - A4 - 15 Sheets

Brand : Epson

Product code: C13S041927

Product name : Ultra Glossy Photo Paper - A4 - 15 Sheets

Ultra Glossy Photo Paper - A4 - 15 Sheets
Epson Ultra Glossy Photo Paper - A4 - 15 Sheets. Finish type: Gloss, Media weight: 300 g/m², Paper size: A4. Quantity per pack: 1 pc(s), Package width: 215 mm, Package depth: 305 mm. Pallet width (UK): 100 cm, Pallet length (UK): 120 cm, Pallet height (UK): 108 cm. Country of origin: Japan



Features		Logistics data	
Paper size	A4	Harmonized System (HS) code	37032000
Finish type *	Gloss	Pallet width (UK)	100 cm
Media weight *	300 g/m²	Pallet length (UK)	120 cm
Sheets per pack	15 sheets	Pallet height (UK)	108 cm
Compatible products	- Expression Premium XP-900 -	Pallet gross width	80 cm
	Expression Premium XP-630 -	Pallet gross length	120 cm
	Expression Premium XP-610 -	Pallet gross height	108 cm
	Expression Premium XP-530 -	Products per pallet	1875 pc(s)
	Expression Photo HD XP-15000 -	Products per pallet (UK)	1875 pc(s)
	Expression Home XP-425 -	Products per pallet layer	300 pc(s)
	Expression Home XP-342 -	Products per pallet layer (UK)	375 pc(s)
	Expression Home XP-332 -	Master (outer) case width	233 mm
	Expression Home XP-245 -	Master (outer) case length	317 mm
	Expression Home XP-235 - Epson	Master (outer) case height	215 mm
	Stylus Photo 2100 - Epson Stylus	Master (outer) case gross weight	1.1 g
	Photo 1500W - Epson Stylus Photo	Products per master (outer) case	25 pc(s)
	1400 - Epson Expression Premium	Minimum order quantity	25 pc(s)
	XP-600 - Epson Expression Home	Other features	
	XP-405WH - Epson Expression		
Packaging data		Country of origin	Japan
Quantity per pack	1 pc(s)		
Package width	215 mm		
Package depth	305 mm		
Package height	5 mm		
Package weight	410 g		



0010343855281



010343855281

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.