




Lenovo 00MM960 network card Internal Fiber 100000 Mbit/s

Brand : Lenovo

Product code: 00MM960

Product name : 00MM960



Mellanox ConnectX-4 2x100GbE/EDR IB QSFP28 VPI


[Lenovo 00MM960 network card Internal Fiber 100000 Mbit/s:](#)

ConnectX-4 from Mellanox is a family of high-performance and low-latency Ethernet and InfiniBand adapters. The ConnectX-4 Lx EN adapters are available in 40 Gb and 25 Gb Ethernet speeds and the ConnectX-4 Virtual Protocol Interconnect (VPI) adapters support either InfiniBand or Ethernet.

These adapters address virtualized infrastructure challenges, delivering best-in-class performance to various demanding markets and applications. Providing true hardware-based I/O isolation with unmatched scalability and efficiency, achieving the most cost-effective and flexible solution for Web 2.0, Cloud, data analytics, database, and storage platforms.

The following figure shows the Mellanox ConnectX-4 2x100GbE/EDR IB QSFP28 VPI Adapter (the standard heat sink has been removed in this photo).


Ports & interfaces		System requirements	
Connectivity technology *	Wired	Compatible operating systems	Microsoft Windows Server 2012 (no SR-IOV support) Microsoft Windows Server 2012 R2 Microsoft Windows Server 2016 Red Hat Enterprise Linux 6 Server x64 Edition, U7 Red Hat Enterprise Linux 7, U2 SUSE LINUX Enterprise Server 11 for AMD64/EM64T, SP4** SUSE LINUX Enterprise Server 12, SP1** VMware ESXi 5.5, U3* VMware ESXi 6.0, U2*
Host interface *	PCI Express		
Interface *	Fiber		
Fiber ports quantity	2		
Fiber optic connector	QSFP28		
PCI Card form factor	Full-height (low-profile)		
Network			
Maximum data transfer rate *	100000 Mbit/s	Operational conditions	
Networking standards *	IEEE 802.1Q, IEEE 802.1Qau, IEEE 802.1Qaz, IEEE 802.1Qbb, IEEE 802.1Qbg, IEEE 802.3ad, IEEE 802.3ae, IEEE 802.3ap, IEEE 802.3az, IEEE 802.3ba	Operating temperature (T-T)	0 - 55 °C
		Storage temperature (T-T)	-40 - 70 °C
		Operating relative humidity (H-H)	0 - 90%
Jumbo frames support	✓	Storage relative humidity (H-H)	0 - 90%
Auto-negotiation	✓	Packaging data	
Design		Quantity per pack	1 pc(s)
		Technical details	
Component for *	Server	Compliance certificates	RoHS
Product colour	Green		
Internal *	✓		
Safety	CB, cTUVus, CE		
Certification	CE, FCC, VCCI, ICES, RCM		



0889488417292



889488417292



8894884172920

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.