APC NetShelter Cable Management, Horizontal Cable Manager, 1U, Single Side with Cover, Black, 482.6 x 44.45 x 165.1 mm

Brand : APC

Product code: AR8612

Product name : APC NetShelter Cable Management, Horizontal Cable Manager, 1U, Single Side with Cover, Black, 482.6 x 44.45 x 165.1 mm

APC NetShelter Cable Management, Horizontal Cable Manager, 1U, Single Side with Cover, Black, 482.6 x 44.45 x 165.1 mm

APC NetShelter Cable Management, Horizontal Cable Manager, 1U, Single Side with Cover, Black, 482.6 x 44.45 x 165.1 mm:


High density 1U, 6-in (150-mm) deep, horizontal cable manager AR8612 with cover.
APC NetShelter Cable Management, Horizontal Cable Manager, 1U, Single Side with Cover, Black, 482.6 x 44.45 x 165.1 mm. Type: Cable management panel, Product colour: Black. Weight: 800 g

Features	
Type *	Cable management panel
Product colour *	Black
Built-in fan	✕
Rack capacity	1U
Hot-swap	✕
On/off switch	✕
Castor wheels	✕
Locking	✕
Certification	TAA, REACH
Weight & dimensions	
Width	483 mm
Depth (max)	16.6 cm

Weight & dimensions	
Height	45 mm
Weight	800 g
Packaging data	
Package width	521 mm
Package depth	200 mm
Package height	77 mm
Package weight	1.05 kg
Technical details	
Total carbon footprint (kg of CO2e)	3.19
Compliance certificates	RoHS
Logistics data	
Harmonized System (HS) code	85389099




7313042915588




0804904115972



804904115972



4053162789036



7313042915601




0804067312591



804067312591




4923213196994



0801947294893



801947294893



0809394597178



809394597178


Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date



0808113973279



808113973279



0731304291558



731304291558

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date