



Lenovo 1000BASE-SX SFP network transceiver module Fiber optic
1000 Mbit/s 850 nm

Brand : Lenovo
Product code: 81Y1622
Product name : 1000BASE-SX SFP

1000Base-SX SFP (mini-GBIC) transceiver module, LC connector

Lenovo 1000BASE-SX SFP network transceiver module Fiber optic 1000 Mbit/s 850 nm:

IBM/Lenovo is a global technology and innovation company, it is the largest technology and consulting employer in the world. IBM offers a wide range of technology and consulting services; a broad portfolio of middleware for collaboration, predictive analytics, software development and systems management; and the world's most advanced servers and supercomputers. Utilizing its business consulting, technology and R&D expertise, IBM helps clients become "smarter" as the planet becomes more digitally interconnected. As a global leader in the PC market, IBM develops, manufactures and markets cutting-edge, reliable, high-quality PC products and value-added professional services that provide customers around the world with smarter ways to be productive and competitive.

Performance		Certificates	
SFP transceiver type *	Fiber optic	Certification	MSA
Maximum data transfer rate *	1000 Mbit/s	Operational conditions	
Interface type *	SFP	Operating temperature (T-T)	0 - 70 °C
Multi-mode fiber (MMF) supported	✓	Storage temperature (T-T)	-40 - 85 °C
Fiber optic connector	LC	Operating relative humidity (H-H)	10 - 80%
SFP transceiver standard	SX	Storage relative humidity (H-H)	10 - 85%
Wavelength	850 nm	Weight & dimensions	
Networking standards	IEEE 802.3, IEEE 802.3ab, IEEE 802.3u	Width	13.4 mm
Cabling technology	1000BASE-SX	Depth	56.5 mm
Auto MDI/MDI-X	✓	Height	8.5 mm
Features		Logistics data	
Hot-Plug support	✓	Harmonized System (HS) code	85369010



4053162240674



0883436100540



883436100540



2002140360004

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.