HP LaserJet 500-sheet Feeder/Tray





Brand : HP **Product family:** LaserJet **Product code:** CF406A

Product name : LaserJet 500-sheet Feeder/Tray

HP LaserJet 500-sheet Feeder/Tray

HP LaserJet 500-sheet Feeder/Tray:

Support the productivity of growing work groups with simple, robust paper input accessories that enable media versatility, from A4 to legal, and allow longer printing without reloading paper.**Reduce trips to the printer to reload paper with this paper input accessory. Print more pages without having to reload paper.**

Automatically print on two different types of paper such as plain paper and glossy brochure paper without manually loading paper trays for each print job.


Save time and improve the performance of individuals and work groups with the increased paper capacity of this 500-sheet paper tray from HP. With more sheets of available paper, users spend less time refilling paper trays.

Features	
Maximum capacity	500 sheets
Media formats	
Letter	✔
Legal	✔
Weight & dimensions	
Weight	4.3 kg
Packaging data	
Package weight	5.3 kg
Package dimensions (WxDxH)	495 x 250 x 468 mm
Package dimensions (W x D x H)	495.3 x 248.9 x 467.4 mm (19.5 x 9.8 x 18.4")
Package weight (imperial)	5.26 kg (11.6 lbs)

Logistics data	
Pallet dimensions (W x D x H)	1200 x 1000 x 2022 mm
Pallet dimensions (W x D x H) (imperial)	1198.9 x 1000.8 x 2021.8 mm (47.2 x 39.4 x 79.6")
Pallet weight (imperial)	191.9 kg (423 lbs)
Master (outer) cases per pallet	8 pc(s)
Layers per pallet	4 pc(s)
Pallet gross weight	192.3 kg
Other features	
Dimensions (WxDxH)	411.3 x 368 x 139.2 mm
Case or master carton quantity	32 pc(s)
Custom media sizes	105 x 148 to 216 x 356 mm
Weight (imperial)	4.31 kg (9.5 lbs)
Size (imperial)	41.1 cm (16.2")




5711045655890



0886112404017



886112404017



0823887423218



823887423218

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date