

Targus THZ779GL tablet case Folio Black

Brand : Targus

Product code: THZ779GL

Product name : THZ779GL

- Case passes military grade 4' drop testing (MIL-STD 810G)*
 - Hard-moulded tray with durable kickstand
 - Advanced corner protection with shock-absorbent TPU
 - Non-slip interior for infinite viewing angles
 - Integrated Surface Pen holder (pen not included)
 - Compatible with Surface Type Cover
 - Compatible with Surface Dock
 - Full access to camera and ports
- 181.1x22x247.6mm, 344.7g, Polycarbonate/TPU, Black



[Targus THZ779GL tablet case Folio Black:](#)

Overview

Lightweight and strong the Targus Protect Case keeps your Microsoft Surface Go protected. From its hardened polycarbonate shell with shock-absorbing materials to advanced corner and side protection, it meets the rigorous MIL-STD-810G standards that protect from sudden drops and accidental slips. With an integrated stand it easily transitions through virtually infinite viewing and typing positions. And, precision cut holes enable you to access all the ports and camera without taking off the case.

Features		Packaging data	
Compatibility *	Surface Go	Package height	292.9 mm
Case type *	Folio	Package weight	350 g
Material *	Polycarbonate, Thermoplastic polyurethane (TPU)	Logistics data	
Product main colour *	Black	Harmonized System (HS) code	84733080
Brand compatibility *	Microsoft	Shipping (inner) case width	19.9 cm
Built-in speaker(s) *	✗	Shipping (inner) case length	12.5 cm
Stand mode *	✓	Shipping (inner) case height	30.5 cm
Protection features	Shock resistant	Products per shipping (inner) case	5 pc(s)
Battery		Master (outer) case width	260 mm
Built-in battery *	✗	Master (outer) case length	410 mm
Weight & dimensions		Master (outer) case height	260 mm
Width	180 mm	Master (outer) case gross weight	8.05 kg
Depth	260 mm	Products per master (outer) case	20 pc(s)
Height	15 mm	Shipping (inner) case net weight	1.92 kg
Weight	350 g	Products per pallet	720 pc(s)
Packaging data			
Package width	20 mm		
Package depth	187 mm		



5051794026702



0092636336165



092636336165

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.