

StarTech.com 4 Port Gigabit Power over Ethernet PCIe Network Card - PSE / PoE PCI Express NIC - TAA

Brand : StarTech.com

Product code: ST4000PEXPSE

Product name : 4 Port Gigabit Power over Ethernet PCIe Network Card - PSE / PoE PCI Express NIC - TAA



StarTech 4 Port Gigabit PoE (Power over Ethernet) Card - PCIe Network Card - PoE / PoE+ Up to 25W Per Port - PCIe NIC - Gigabit Ethernet Card , TAA (ST4000PEXPSE)

StarTech.com 4 Port Gigabit Power over Ethernet PCIe Network Card - PSE / PoE PCI Express NIC - TAA. Internal. Connectivity technology: Wired, Host interface: PCI Express, Interface: Ethernet. Maximum data transfer rate: 2000 Mbit/s



Ports & interfaces		System requirements	
Connectivity technology *	Wired	Server operating systems supported	Windows Server 2003, Windows Server 2008 R2, Windows Server 2012, Windows Server 2012 R2, Windows Server 2016, Windows Server 2019
Host interface *	PCI Express		
Interface *	Ethernet		
Ethernet LAN (RJ-45) ports	4		
PCI Card form factor	Full-height		
Network		Operational conditions	
Maximum data transfer rate *	2000 Mbit/s	Operating temperature (T-T)	0 - 55 °C
Networking standards *	IEEE 802.1p, IEEE 802.1Q, IEEE 802.3, IEEE 802.3ab, IEEE 802.3at, IEEE 802.3az, IEEE 802.3u, IEEE 802.3x	Storage temperature (T-T)	-40 - 75 °C
		Operating relative humidity (H-H)	10 - 90%
Ethernet LAN	✓	Weight & dimensions	
Ethernet LAN data rates	10,100,1000 Mbit/s	Width	18 mm
Cabling technology	10/100/1000BaseT(X)	Depth	243 mm
Wake-on-LAN ready	✓	Height	120 mm
Auto MDIX IEEE	✓	Weight	102 g
Full duplex	✓	Packaging data	
Jumbo frames support	✓	Drivers included	✓
Jumbo frames	9000	Package width	188 mm
Design		Package depth	296 mm
Internal *	✓	Package height	66 mm
Chipset	RTL8111E	Package weight	428 g
LED indicators	Link, PoE	Packaging content	
Certification	CE, FCC, REACH, TAA	Manual	✓
Power		Technical details	
Output voltage	48 V	Compliance certificates	RoHS
		Logistics data	
		Harmonized System (HS) code	85176990

System requirements		Other features	
Windows operating systems supported	Windows 10, Windows 10 Education, Windows 10 Education x64, Windows 10 Enterprise, Windows 10 Enterprise x64, Windows 10 Home, Windows 10 Home x64, Windows 10 IOT Core, Windows 10 Pro, Windows 10 Pro x64, Windows 10 x64, Windows 2000, Windows 2000 Professional, Windows 7, Windows 7 Enterprise, Windows 7 Enterprise x64, Windows 7 Home Basic, Windows 7 Home Basic x64, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows 7 x64, Windows 8, Windows 8 Enterprise, Windows 8 Enterprise x64, Windows 8 Pro, Windows 8 Pro x64, Windows 8 x64, Windows 8.1, Windows 8.1 Enterprise, Windows 8.1 Enterprise x64, Windows 8.1 Pro, Windows 8.1 Pro x64, Windows 8.1 x64, Windows Vista Business, Windows Vista Business x64, Windows Vista Enterprise, Windows Vista Enterprise x64, Windows Vista Home Basic, Windows Vista Home Basic x64, Windows Vista Home Premium, Windows Vista Home Premium x64, Windows Vista Ultimate, Windows Vista Ultimate x64, Windows Vista x64, Windows XP, Windows XP Home, Windows XP Home x64, Windows XP Professional, Windows XP Professional x64	Buffer size	48 KB
		Peripheral (Molex) power connectors (4-pin)	1
		Number of SATA power connectors	1
Linux operating systems supported		✓	



0065030855150



065030855150

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.