

Alienware AW510K keyboard Gaming USB Black, White

Brand : Alienware

Product code: AW510K-W-WW

Product name : AW510K

USB, RGB LED, 1000Hz, Cherry MX Red, 2m, 910g, Lunar Light

Alienware AW510K. Keyboard form factor: Full-size (100%). Keyboard style: Straight. Connectivity technology: Wired, Device interface: USB, Keyboard key switch: Mechanical. Backlight type: RGB LED. Cable length: 2 m. Recommended usage: Gaming. Product colour: Black, White



Keyboard		Features	
Keyboard key switch technology	Cherry MX Red	Cable length	2 m
Recommended usage *	Gaming	Anti-ghosting	✓
Connectivity technology *	Wired	Power	
Device interface *	USB	Power source type *	USB
Keyboard key switch *	Mechanical	Mouse	
Pointing device *	✗	Mouse included *	✗
Keyboard form factor *	Full-size (100%)	System requirements	
Numeric keypad *	✓	Windows operating systems supported	Windows 10
Keyboard keys operating life	50 million characters	Weight & dimensions	
Keyboard key profile	Low-profile	Keyboard dimensions (WxDxH)	467 x 156.2 x 29.4 mm
Windows keys	✓	Keyboard weight	910 g
Programmable hot keys	✓	Packaging data	
Multimedia keys	✓	Package width	505 mm
Rollover	N-key rollover	Package depth	52 mm
Design		Package height	225 mm
Backlight *	✓	Package weight	1.4 kg
Backlight type	RGB LED	Package type	Box
Adjustable backlight	✓	Packaging content	
Keyboard style	Straight	Number of products included *	1 pc(s)
Adjustable keyboard height	✓	Other features	
Product colour *	Black, White	Compatibility	Alienware M15, M17, Area-51, Aurora, Aurora Ryzen Edition
Surface coloration	Monochromatic	Logistics data	
		Harmonized System (HS) code	84716060



5397184218068



0884116349419



884116349419

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.