HP Color Laser MFP 179fnw





Brand : HP **Product family:** Color Laser **Product code:** 4ZB97A#B19

Product name : Color Laser MFP 179fnw

- Scan to PDF
- Print, copy, scan, fax
- Print speed up to 19 ppm (black) and 4 ppm (colour)
- Up to 600 x 600 dpi 4 bits

Color Laser MFP 179fnw

HP Color Laser MFP 179fnw:

Get productive MFP performance – world's smallest in-class.[1] Print, scan, copy, and fax, produce high-quality colour results, and print and scan from your phone.[2]

Dynamic security enabled printer Certain HP printers are intended to work only with cartridges that have a new or reused HP chip or electronic circuitry. These printers use dynamic security measures to block cartridges using a non-HP chip or electronic circuitry. Periodic firmware updates will maintain the effectiveness of these measures and block cartridges that previously worked. Reused HP chips and electronic circuitry enable the use of reused, remanufactured, and refilled cartridges.

Printing	
Duplex printing mode	Manual
Print resolution colour	600 x 600 DPI
Print resolution black	600 x 600 DPI
Print technology *	Laser
Printing *	Colour printing
Duplex printing *	✔
Maximum resolution *	600 x 600 DPI
Print speed (black, normal quality, A4/US Letter) *	18 ppm
Print speed (colour, normal quality, A4/US Letter)	4 ppm
Warm-up time	38 s
Time to first page (black, normal)	12.4 s
Time to first page (colour, normal)	25.3 s
Print margins (top, bottom, right, left)	5 mm
N-in-1 print function	✔
Watermark printing	✔
Secure printing	✔
Booklet printing function	✔
Poster printing function	✔

Copying	
Duplex copying *	✔
Copying *	Colour copying
Maximum copy resolution *	600 x 600 DPI
Copy speed (black, normal quality, A4)	18 cpm
Copy speed (colour, normal quality, A4)	4 cpm
Time to first copy (black, normal)	12.6 s
Time to first copy (colour, normal)	32.1 s
Maximum number of copies	999 copies

Performance	
Maximum internal memory	128 MB
Internal memory *	128 MB
Built-in processor	✔
Processor frequency	800 MHz
Sound power level (printing)	6.5 dB

Design	
Product colour *	Black, White
Market positioning *	Home & office
Built-in display *	✔
Display	LCD
Display number of lines	2 lines
Control type	Buttons

Power	
Power consumption (printing)	300 W
Power consumption (ready)	38 W
Power consumption (sleep)	1.9 W
Power consumption (off)	0.2 W
Energy Star Typical Electricity Consumption (TEC)	0.876 kWh/week
AC input voltage	220 - 240 V
AC input frequency	50/60 Hz

Brand-specific features	
HP Auto-On/Auto-Off	✔
HP Dynamic security	✔
HP Security tools	Password-protected network embedded Web server; Enable/disable Network ports; SNMPv1 community password change; SNMPV2&V3; IPSec; Filtering : MAC, IPv4, IPv6

Copying	
Copier resize	25 - 400%
N-in-1 copy function	✔
N-in-1 copy function (N=)	4, 2
ID-card copy function	✔
Background adjustment function	✔
Auto fit function	✔

Scanning	
Scanning *	Colour scanning
Optical scanning resolution *	600 x 600 DPI
Maximum scan resolution	19200 x 19200 DPI
Maximum scan area	216 x 297 mm
Scanner type *	Flatbed & ADF scanner
Scan technology	CIS
Scan to	Software, TWAIN, WIA
Image formats supported	JPG, TIFF
Document formats supported	PDF
Input colour depth	24 bit
Greyscale levels	256
Scan drivers	TWAIN, WIA
TWAIN version	1.9

Fax	
Faxing *	Mono faxing
Fax resolution (black)	300 x 300 DPI
Modem speed	33.6 Kbit/s
Fax memory	400 pages
Auto-redialing	✔
Speed dialling	✔
Fax forwarding	✔
Fax delayed sending	✔
Auto reduction	✔
Distinctive ring	✔

Features	
Recommended duty cycle	100 - 500 pages per month
Maximum duty cycle *	20000 pages per month
Duplex functions *	Scan
Digital sender	✔
Number of print cartridges *	4
Printing colours *	Black, Cyan, Magenta, Yellow
Page description languages	SPL
All-In-One-multitasking	✔
Country of origin	China
Replacement cartridges	HP 117A Black Original Laser Toner Cartridge (1,000 pages) W2070A; HP 117A Cyan Original Laser Toner Cartridge (700 pages) W2071A; HP 117A Yellow Original Laser Toner Cartridge (700 pages) W2072A; HP 117A Magenta Original Laser Toner Cartridge (700 pages) W2073A
HP segment	Home office

Input & output capacity	
Total number of input trays *	1
Total input capacity *	150 sheets
Total output capacity *	50 sheets
Paper tray 1 input capacity	150 sheets
Paper input type	Paper tray
Auto document feeder (ADF)	✔
Auto document feeder (ADF) input capacity	40 sheets

Brand-specific features	
HP GTIN (EAN/UPC) with options	(ABT) 193015507333; (ABY) 193015507340; (ACQ) 193015507371; (B13) 193905621620; (B19) 193015507388; (BAZ) 193015507395
HP GTIN (EAN/UPC)	193015507333, 193015507340, 193015507371, 193905621620, 193015507388, 193015507395

System requirements	
Windows operating systems supported	Windows 8, Windows 11
Mac operating systems supported	Mac OS X 10.11 El Capitan, Mac OS X 10.12 Sierra, Mac OS X 10.13 High Sierra, Mac OS X 10.14 Mojave, MacOS
Server operating systems supported	Windows Server 2008 R2, Windows Server 2012, Windows Server 2016

Operational conditions	
Operating relative humidity (H-H)	10 - 80%
Recommended operating temperature range (T-T)	15 - 27 °C
Storage temperature (T-T)	-20 - 40 °C
Operating temperature (T-T)	10 - 30 °C

Certificates	
Certification	EN 61000-3-2:2014, EN 61000-3-3:2013, EN55024:2010, EN 55032:2012/AC:2013, 47 CFR Part 15, Subpart B I ANSI C63.4-2009, ICES-003 Issue 5, KN32, KN35, CISPR22:2008, CISPR32:2012, CNS 13438 (Other EMC approvals as required by individual countries)

Sustainability	
Sustainable technologies and materials	Mercury free
Doesn't contain	Mercury

Carbon footprint	
Total carbon footprint (kg of CO2e)	180
Carbon emissions, manufacturing (kg of CO2e)	108
Carbon emissions, logistics (kg of CO2e)	5
Carbon emissions, end-of-life (kg of CO2e)	19
Total carbon emissions, w/o use phase (kg of CO2e)	45

Weight & dimensions	
Width	406 mm
Depth	363 mm
Height	344.1 mm
Weight	14.1 kg

Packaging data	
Package width	501 mm
Package depth	466 mm
Package height	440 mm
Package weight	17.4 kg

Packaging content	
Cartridge(s) included	✔
Included cartridge capacity (black)	700 pages
Included cartridge capacity (CMY)	500 pages
Cables included	AC
Manual	✔

Input & output capacity

Maximum number of input trays	1
Maximum input capacity	150 sheets
Maximum output capacity	50 sheets

Paper handling

Maximum ISO A-series paper size *	A4
Maximum print size	216 x 356 mm
Paper tray media types *	Plain paper, Glossy paper, Bond paper, Recycled paper, Labels, Heavy paper, Lightweight paper
ISO A-series sizes (A0...A9) *	A4, A5, A6
ISO B-series sizes (B0...B9)	B5
Non-ISO print media sizes	Oficio
JIS B-series sizes (B0...B9)	B5
Custom media width	76 - 216 mm
Custom media length	148.5 - 356 mm
Paper tray media weight	60 - 220 g/m²
Envelope feeder	No

Ports & interfaces

Standard interfaces	USB 2.0
Direct printing *	✔
USB port	✔

Network

Wi-Fi *	✔
Ethernet LAN *	✔
Cabling technology	10/100Base-T(X)
Ethernet LAN data rates	10,100 Mbit/s
Wi-Fi standards	Wi-Fi 4 (802.11n), 802.11g, 802.11b
Wi-Fi Direct	✔
Security algorithms	SNMPv2, SNMP, IPSec
Mobile printing technologies	Mopria Print Service, Apple AirPrint, Google Cloud Print

Packaging content

Power cord included	✔
Warranty card	✔
Quick installation guide	✔
User guide	✔
Bundled software	Common Installer, V3 Print Driver with Lite SM, TWAIN/WIA Driver, HP MFP Scan, HP LJ Network PC-FAX, OCR program

Logistics data

Harmonized System (HS) code	84433100
Pallet gross weight	357 kg
Master (outer) cases per pallet	20 pc(s)
Layers per pallet	5 pc(s)
Products per pallet	20 pc(s)

Technical details


Box contents	HP Color Laser MFP 179fnw; Preinstalled introductory HP Laser Printer Black print cartridge (700 pages); HP Laser Printer Cyan print cartridge (500 pages); HP Laser Printer Yellow print cartridge (500 pages); HP Laser Printer Magenta print cartridge (500 pages); Imaging drum; Toner collection unit; Setup poster; Reference guide; Support flyer; Warranty guide; No CD-ROM; Power cord; USB cable; Tel line cable
Master (outer) cases per pallet layer	4 pc(s)
Compliance certificates	CECP, CE
General Product Safety Regulation (GPSR) URL	https://support.hp.com/gb-en/product/setup-user-guides/hp-color-laser-mfp-170-printer-series/model/24494369?sku=4ZB97A ; http://h10032.www1.hp.com/ctg/Manual/c06266695.pdf ; http://h10032.www1.hp.com/ctg/Manual/c06270941.pdf

Other features

Number of users	5 user(s)
Custom media sizes	76 x 148.5 to 216 x 356 mm
Pallet dimensions (W x D x H)	1014 x 944 x 2202 mm
Recommended system requirements	PC; Windows 10; 8.1; 8; 2 GB available hard disk space; CD-ROM/DVD drive or Internet connection; USB port; Internet Explorer. AppleOS X El Capitan (v10.11); macOS Sierra (v10.12); macOS High Sierra (v10.13); 1.5 GB available hard disk space; Internet required; USB.
Compatible operating systems	Windows 11; Windows 8; macOS 10.11 El Capitan; macOS 10.12 Sierra; macOS 10.13 High Sierra; macOS 10.14 Mojave
Typical electricity consumption (TEC) number	0.876 kWh/Week (Blue Angel); 1.093 kWh/Week (Energy Star)
UNSPSC-code	43212110
Electromagnetic compatibility	EN 61000-3-2:2014, EN 61000-3-3:2013, EN55024:2010, EN 55032:2012/AC:2013, 47 CFR Part 15, Subpart B I ANSI C63.4-2009, ICES-003 Issue 5, KN32, KN35, CISPR22:2008, CISPR32:2012, CNS 13438 (Other EMC approvals as required by individual countries)



0193015507388



193015507388

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date