

StarTech.com 20in (50cm) USB A to C Charging Cable, Coiled Heavy Duty Fast Charge & Sync, High Quality USB 2.0 A to USB Type-C Cable, Rugged Aramid Fiber, Durable Male to Male USB Cable

Brand : StarTech.com

Product code: R2ACC-50C-USB-CABLE

Product name : 20in (50cm) USB A to C Charging Cable, Coiled Heavy Duty Fast Charge & Sync, High Quality USB 2.0 A to USB Type-C Cable, Rugged Aramid Fiber, Durable Male to Male USB Cable

StarTech.com 1.6ft (50cm) USB-A to USB-C Fast Charging Cable, Rugged, Coiled, Charge & Sync, 3A, USB 2.0, TPE Jacket

StarTech.com 20in (50cm) USB A to C Charging Cable, Coiled Heavy Duty Fast Charge & Sync, High Quality USB 2.0 A to USB Type-C Cable, Rugged Aramid Fiber, Durable Male to Male USB Cable. Cable length: 0.5 m. Connector 1: USB A, Connector 2: USB C, USB version: USB 2.0, Maximum data transfer rate: 0.48 Gbit/s, Connector contacts plating: Nickel, Product colour: Black



Features		Weight & dimensions	
USB version *	USB 2.0	Weight	28 g
Connector 1 *	USB A	Packaging data	
Connector 2 *	USB C	Package width	125 mm
Connector 1 gender *	Male	Package depth	220 mm
Connector 2 gender *	Male	Package height	17 mm
Connector 1 form factor	Straight	Package weight	30 g
Connector 2 form factor	Straight	Packaging content	
AWG wire size	32/22	Quantity per pack *	1 pc(s)
Connector contacts plating	Nickel	Operational conditions	
Cable jacket material	Thermoplastic elastomer (TPE)	Operating temperature (T-T)	0 - 80 °C
Cable shielding	Aluminum mylar foil	Storage temperature (T-T)	0 - 80 °C
Maximum data transfer rate	480 Mbit/s	Logistics data	
Maximum data transfer rate	0.48 Gbit/s	Products per master (outer) case	200 pc(s)
Plug and Play	✓	Master (outer) case width	380 mm
Product colour *	Black	Master (outer) case length	430 mm
Weight & dimensions		Master (outer) case height	290 mm
Cable length *	0.5 m	Harmonized System (HS) code	84733080
Cable diameter	3.1 mm		



0065030893527



065030893527

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.